

42U Open Frame Server Rack - 994.5lbs capacity - 4 Post Adjustable Depth (22" to 40") Network Equipment Rack

Product ID: 4POSTRACKBK



StarTech.com's DuraRak 42U Adjustable 4 Post Open Server Rack offers a solid, versatile solution for mounting servers and other networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This full size (42U) rack offers adjustable posts for maximum flexibility, and an open frame design with heavy gauge mounting rails to ensure exceptional structural stability.

To ensure broad compatibility, the 42U rack features an industry standard design for compatibility with equipment from popular manufacturers.

A cost-effective solution, the rack is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty, plus the rack is flat-packed for easier handling and assembly.

For even more versatility, StarTech.com offers an optional 4pc Caster Kit (4POSTCASTER) that can be installed to the bottom of the 42U server rack.

Certifications, Reports and Compatibility

Applications

- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

Features



- Open frame design with heavy gauge mounting rails provides exceptional structural stability
- Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature
- TAA compliant for GSA Schedule purchases
- Easily route, manage and access your equipment cables without any obstruction
- Adjustable mounting rails ensure compatibility with many rack mount equipment
- Heavy-duty base with holes allow you to bolt the server rack to the floor when mounting heavy rack mount equipment

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	42U
Special Features	Adjustable Mounting Rails Base Plate with Floor-Anchoring Holes Casters (Optional) Easy Assembly
Mounting Rail Profile	C-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	994.5 lb [450 kg]
-----------------	-------------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements



Product Length	39.2 in [99.5 cm]
Product Width	22.4 in [57.0 cm]
Product Height	6.5 ft [2.0 m]
Weight of Product	102.2 lb [46.3 kg]
Maximum Mounting Depth	39.4 in [100 cm]
Minimum Mounting Depth	22.9 in [58.2 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	6.9 ft [2.1 m]
Package Width	25.8 in [65.5 cm]
Package Height	6.8 in [17.2 cm]
Shipping (Package) Weight	112.3 lb [50.8 kg]

What's in the Box

Included in Package	Front/Rear Frame
	Floor Plates
	Adjustable Horizontal Arm
	Floor Mounting Brackets
	M8 Hex (Allen) key
	M8x25 Hex Socket Screws
	M5x15 Truss Head Screws
	Bushing Caps
	M5 Screws
	M5 Cage Nuts

****Product appearance and specifications are subject to change without notice.***