

Refurbished 12U 4 Post Open Frame Rack with Adjustable Posts & Casters

Product ID: 4POSTRK12AR



The 4POSTRACK12A Open Frame Rack offers a durable, yet flexible open-air housing for rack-mount servers and networking equipment. The rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform with two adjustable posts for variable mounting depths.

Providing a universal design that's compatible with equipment from popular manufacturers, this EIA-RS-310C compliant open rack ships flat packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, this 12U rack ships with 4 swiveling casters and has a total height of less than 26" (661mm) which allows the rack to be rolled under most desks or work benches with little effort.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

Certifications, Reports and Compatibility



Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Useful for point of sale applications, specifically mounting equipment under the check-out counter

- Suitable for rackmount equipment where security at the rack level is not required
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Mounting equipment under a desk/workspace
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Swivel Casters included
- Two Adjustable Rails for variable mounting depths
- Open frame design easy access and greater air flow
- Shipped as a flat pack for easier handling
- Less than 3ft tall, perfect for rolling under desks or benches
- Heavy gauge mounting rails

Hardware

Warranty	None
Wallmountable	No
Rack Type	4-Post
Frame Type	Steel
U Height	12U
Special Features	Adjustable Mounting Rails
	Casters (Included)
	Easy Assembly
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	595.4 lb [270 kg]
---------------------------------	-------------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	35.9 in [91.3 cm]
Product Width	21.0 in [53.4 cm]
Product Height	23.1 in [58.6 cm]
Weight of Product	34.4 lb [15.6 kg]
Maximum Mounting Depth	35.9 in [91.3 cm]
Minimum Mounting Depth	3.8 in [9.7 cm]
Product Height with Casters	25.9 in [65.7 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	36.3 in [92.1 cm]
Package Width	24.4 in [62.0 cm]
Package Height	6.5 in [16.4 cm]
Shipping (Package) Weight	41.0 lb [18.6 kg]

What's in the Box

Included in Package	2 - Front/Read Frame
	4 - Assembly Post
	2 - Adjustable Rails
	4 - Casters
	52 - 1/4-20 x 12 Hex Bolts
	52 - 1/4" Washers

1 - Pack of M6 Cage Nuts and Cab Screws (16 each)

16 - KEP Nuts

**Warranty
Information**

Warranty

Refurbished 90 Days

****Product appearance and specifications are subject to change without notice.***