

4-Slot USB-C SD Card Reader - USB 3.1 (10Gbps) - SD 4.0, UHS-II

Product ID: 4SD4FCRU31C



This USB-C SD card reader lets you access four SD cards simultaneously. The card reader transfers files between your USB-C, Thunderbolt 3 or USB-A laptop or desktop computer and the reader.

The reader features SD 4.0 and UHS-II support. It reads and writes to and from the cards at speeds of up to 312MB/s. The reader also supports USB 3.1 connection speeds of up to 10Gbps to ensure maximum transfer rates between the computer and the reader, while simultaneously accessing all four cards.

The card reader is also backward compatible with earlier versions of USB (3.0, 2.0 and 1.1).

The card reader supports all SD cards: SD (Secure Digital), SDHC (Secure Digital High Capacity) and SDXC (Secure Digital Extended Capacity). It also supports UHS cards, and is backward compatible with older SD card versions.

The card reader will also support the following card types when connected through an adapter:

- microSD
- miniSD
- MMCmobile
- RS-MMC
- MMCplus

The small footprint design fits in nicely with your workstation. Place the card reader on your desk without taking up too much space.

4SD4FCRU31C comes with a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Access four SD cards simultaneously
- Download and edit photos and videos
- Back up documents and critical data from multiple users
- Deploy system updates in batches
- Distribute content to multiple employees

Features

- Save time and access four SD cards simultaneously with this multi SD card reader
- Ensure maximum transfer rates while accessing all four cards with connection speeds of up to 10Gbps
- Perform fast read and/or writes with support for SD 4.0, UHS-II and bus speeds up to 312MB/s
- Access more cards, the card reader supports all SD types: SD, SDHC, and SDXC
- Easily integrate this USB-C SD card reader into your workstation with its compact design

Hardware

Warranty	2 Years
Interface	USB 3.1 Gen 2
Chipset ID	Genesys Logic - GL3590 Genesys Logic - GL3227

Performance

Type and Rate	USB 3.1 Gen 2 - 10 Gbit/s UHS-II (SD 4.0; 312MB/s)
Memory Media Type	SDXC (Secure Digital eXtended Capacity) SDHC (Secure Digital High Capacity) SD/MMC (Secure Digital/Multimedia Card)

Connector(s)

Drive Connectors	SD / MMC Slot
------------------	---------------



Host Connectors	USB Type-C (24 pin) USB 3.1 (10Gbps)
-----------------	--------------------------------------

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	Activity
----------------	----------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1 A
Output Voltage	5 DC
Output Current	2.4 A
Center Tip Polarity	Positive
Plug Type	B

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~60% RH

Physical Characteristics

Product Length	7.0 in [17.7 cm]
Product Width	2.8 in [70.0 mm]
Product Height	0.7 in [17.0 mm]
Weight of Product	11.8 oz [335.0 g]

Packaging Information

Package Length	7.7 in [19.5 cm]
Package Width	5.6 in [14.2 cm]



Package Height	2.0 in [50.0 mm]
Shipping (Package) Weight	19.2 oz [543.0 g]

What's in the Box

Included in Package	SD Card Reader
	Quick-Start Guide
	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	3 ft [0.9 m] USB-C to USB-C Cable
	3 ft [0.9 m] USB-A to USB-C Cable

****Product appearance and specifications are subject to change without notice.***

