

Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/ST - 10 m

Produkt ID: 50FIBLCST10



The 50FIBLCST10 10m LSZH LC to ST Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication

Funktioner

- 1x LC MM male connector
- 1x ST MM male connector
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

Hårdvara

| | |
|--------------------|---------------------------------------|
| Garantipolicy | Lifetime |
| Brandteknisk klass | LSZH-klassad (Low Smoke Zero Halogen) |
| Fiberstorlek | 50/125 |

Prestanda

| | |
|----------------------------------|----------------|
| Maximal dataöverföringshastighet | 10Gbps |
| Kabelklassificering | 1Gbps / 10Gbps |
| Fiberklassificering | OM2 |
| Fibertyp | Multiläge |

Kontakt(er)

| | |
|-------------|-----------------------|
| Connector A | Fiberoptisk LC duplex |
| Connector B | Fiberoptisk ST duplex |

Miljö

| | |
|----------------------|-------------------------------|
| Drifttemperatur | -20°C to 60°C (-4°F to 140°F) |
| Förvaringstemperatur | -20°C to 60°C (-4°F to 140°F) |
| Luftfuktighet | 0~90% RH |

Utseende



| | |
|--------------|----------------|
| Färg | Orange |
| Kabellängd | 32.8 ft [10 m] |
| Produktlängd | 32.8 ft [10 m] |
| Produktvikt | 4.8 oz [136 g] |

Förpackning

| | |
|-------------------------|----------------|
| Förpackningsantal | 1 |
| Package Length | 8.7 in [22 cm] |
| Package Width | 7.9 in [20 cm] |
| Package Height | 1.1 in [28 mm] |
| Fraktvikt (förpackning) | 5.1 oz [145 g] |

Vad det är i lådan

| | |
|-----------------|---|
| Ingår i paketet | 10m Multimode 50/125 Duplex Fiber Patch Cable LC – ST |
|-----------------|---|

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

