


5m Multimode 50/125 Duplex Fiber Patch Cable SC-SC

Product ID: 50FIBSCSC5



Your company's backbone is its Network. Without a stable, reliable network your company can't communicate. A lack of communication means a loss of revenue. What do you do now? Enter the StarTech.com duplex 50/125 Multimode Fiber Optic patch cable assembly. This product provides the necessary link between Fiber networking devices for high-speed, long-distance networks. Ideal for Gigabit networks, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability. This cable has the same lifetime warranty that applies to all StarTech.com cables.

Certifications, Reports and Compatibility



Applications

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- Attenuation loss meets or exceeds industry standards
- Immune to electricity interference
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty

Hardware

Warranty	Lifetime
Fiber Size	50/125
Fiber Classification	OM2

Performance

Type	Multi Mode
------	------------

Connector(s)

Connector A	1 - Fiber Optic SC Duplex
Connector B	1 - Fiber Optic SC Duplex

Physical Characteristics

Color	Orange
Cable Length	16.4 ft [5 m]
Product Length	16.4 ft [5.0 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	0.0 oz [0.0 g]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.8 in [2.0 cm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	3.5 oz [100.0 g]

**Warranty
Information**

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***