UL Listed Extendable TV Wall Mount for up to 65-inch 176lb (80kg) Displays, Easy Rear Access, Laterally Adjustable Bracket Supports up to VESA 600x400

Product ID: 65ULE-TV-WALL-MOUNT



UL listed TV mount supports up to 65-inch displays and 176lb (80kg), giving you a sturdy platform with anti-theft design for meeting rooms, classrooms, and digital signage that need a strong, stable wall bracket. Keep the TV close to the wall at a 2.1in (5.3cm) profile or extend up to 6.8in (17.2cm) to match your setup.

This TV mount is tested and certified by UL Solutions to UL 2442 and complies with a 4x weight safety factor over its rated load, providing assurance for commercial and public-space installations

The extendable arms create ample working room behind the TV, providing easy access to AV, power, and network connections for cable installation and reconfiguration. Integrated quick-release cords allow the display to be removed and reinstalled quickly for servicing when needed.

Use the side-to-side sliding design to help center the display on wood stud, concrete, or brick walls. VESA compatibility from 200x200 to 600x400mm helps standardize installs across a wide range of TVs.

Fine-tune the viewing angle with tilt from +10 to -15 and swivel from +10 to -10 to improve visibility across the room.

Certifications, Reports and Compatibility

Applications

Features

• Securely Mount Large, Heavy Displays: This UL listed TV mount supports up to 65-inch displays and 176lb (80kg), giving you a sturdy platform with anti-theft design for meeting rooms, classrooms, and digital signage

• Mount with Confidence: This TV mount is tested and certified by UL Solutions to UL 2442 and complies with a 4x weight safety factor over its rated load, providing assurance for commercial and public-space installations

• Easy Service Access: Extendable arms reach up to 6.8in (17.2cm), creating ample space for rear TV access and cable management; Integrated quick-release cords make it easy to remove and reinstall the display for servicing and maintenance

• Center the TV on Any Wall Type: Use the side-to-side sliding design to center the TV on wood stud, concrete, or brick walls, while VESA compatibility from 200x200 to 600x400 enables supports for a wide range of displays

• Adjust the Screen for Better Viewing: Adjustable TV bracket lets you fine-tune positioning with tilt from +10 to -15 and swivel from +10 to -10 for better visibility across the room

General		
	UPC	065030922982
	Warranty	5 Years
Physical & Environmental		
	Color	Black
	Construction Material	Steel
	Product Length	28.5 in [72.5 cm]
	Product Width	2.1 in [53 mm]
	Product Height	13.8 in [35 cm]
	Weight of Product	33.4 lb [15.2 kg]
Performance		
	Anti-theft	Yes
	Minimum Display Size	37"
	Maximum Display Size	65"
	Video Wall	No
	Display Tilt	+10 / -15
	Height Adjustment	Yes

	Display Swivel	+10 / -10
Hardware		
	Number of Displays	1
	Mounting Options	Wall-Mount
	Minimum Profile from Wall	2.1 in [53 mm]
	VESA Hole Pattern(s)	200x200 mm
		300x200 mm
		300x300 mm
		400x200 mm
		400x300 mm
		400x400 mm
		600x400 mm
Packaging & In-the-Box		
	Included in Package	1 - TV Mounting Assembly, Right
		1 - TV Mounting Assembly, Left
		2 - Horizontal Brackets
		2 - Vertical Brackets
		1 - Level
		1 - Spirit/Buble Level
		1 - 4mm Hex Key
		1 - 6mm Hex Key
		1 - Wrench
		4 - M6x8mm Screws
		4 - M6x14mm Screws
		4 - M8x16mm Screws
		4 - M6x30mm Screws

	4 - M8x35mm Screws
	4 - Washers
	4 - Small Spacers
	4 - Short Spacers
	4 - Large Spacers
	4 - Long Spacers
	6 - Wall Mounting Screws
	6 - Wall Anchors
	6 - Wall Mounting Washers
	1 - Wall Mounting Template
	1 - Product Documentation
Package Width	5.2 in [13.3 cm]
Package Depth	30.4 in [77.3 cm]
Package Height	3.0 in [75 mm]
Shipping (Package) Weight	12.2 lb [5.6 kg]

Product appearance and specifications are subject to change without notice.