

1.5 m CAT6a Patch Cable - Shielded (STP) - 100% Copper Wire - Snagless Connector - Black

Product ID: 6ASPAT150CMBK



This black 1.5m CAT6a cable meets all Category 6a cable specifications. It ensures reliable 10Gb connections between your network devices.

Rated for up to 500MHz frequency, each CAT6a STP cord is more than suitable for 10GBase-T Ethernet networks.

Built for quality performance, the cable features 100% copper and foil-shielded, twisted-pair wiring. The cable is designed to keep the data signals travelling through your network free from noise and interference. It's perfect in environments that are prone to large amounts of electromagnetic interference (EMI/RFI).

This CAT6a patch cable is built using 100% copper wire and is tested to comply with ANSI/TIA 568 C.2 Category 6a requirements. We don't use copper-clad aluminum (CCA) wire which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

For trouble-free cable runs, this durable cable features snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

The CAT6a Ethernet cable also features moulded boots that offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

6ASPAT150CMBK is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect PoE-enabled devices to 10Gb networks
- Connect servers to a Storage Area Network (SAN)
- Deliver data, voice and video over 10 Gigabit networks
- Connect between computers, hubs, routers and patch panels

Features

- Shield your data against noise and EMI/RFI interference using this CAT6a Ethernet cable
- Supports 10GBase-T Ethernet networks
- Protect your network and equipment with 100% copper wire CAT6a cables
- Tested to comply with ANSI/TIA 568 C.2 CAT6a requirements
- RJ45 connector-clip protectors prevent cable snags and breaks during installation

Hardware

| | |
|-----------------------|-----------------------------|
| Warranty | Lifetime |
| Number of Conductors | 4 Pair STP |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-polyester foil |
| Fire Rating | CMG Rated (General Purpose) |
| Cable Type | Shielded Snag-less |

Performance

| | |
|--------------|------------------|
| Cable Rating | CAT6a - 10Gbit/s |
|--------------|------------------|

Connector(s)

| | |
|-------------|-----------|
| Connector A | 1 - RJ-45 |
| Connector B | 1 - RJ-45 |

Physical Characteristics

| | |
|-------|-------|
| Color | Black |
|-------|-------|

| | |
|-------------------|--------------------|
| Wire Gauge | 26 AWG (0.404 mm) |
| Conductor Type | Stranded Copper |
| Cable Length | 4.9 ft [1.5 m] |
| Product Length | 59.1 in [150.0 cm] |
| Product Width | 0.5 in [1.2 cm] |
| Product Height | 0.5 in [1.3 cm] |
| Weight of Product | 2.4 oz [67 g] |

Packaging Information

| | |
|---------------------------|-----------------|
| Package Quantity | 1 |
| Package Length | 7.9 in [20 cm] |
| Package Width | 8.7 in [22 cm] |
| Package Height | 0.0 in [0.1 mm] |
| Shipping (Package) Weight | 2.7 oz [77 g] |

What's in the Box

| | |
|---------------------|-----------------|
| Included in Package | 1 - CAT6a Cable |
|---------------------|-----------------|

**Product appearance and specifications are subject to change without notice.*