

6-Slot Thunderbolt 3 SD Card Reader - Portable

Product ID: 6SD4FCRTB3C



This Thunderbolt 3 SD card reader and writer lets you access up to six SD cards at the same time from your laptop. It's perfect for when you are working offsite on assignment.

The reader is also ideal for creative professionals such as photographers and videographers who work with 4K and 3D content.

Access your photos and videos anywhere you go. The portable SD card reader has a sleek, compact design for maximum convenience. The integrated Thunderbolt 3 cable lets you quickly access your data without having to stop and find a cable.

Plus, the reader is powered through the Thunderbolt 3 port on your laptop. There's no need to carry a separate power adapter.

The 6-slot Thunderbolt 3 card reader supports all SD cards: SD (Secure Digital), SDHC (Secure Digital High Capacity) and SDXC (Secure Digital Extended Capacity). Each slot is UHS-II enabled so that you can access data at up to UHS-II speeds.

The reader also supports Micro SD cards when connected through an adapter.

The reader transfers files between a Thunderbolt 3 computer or tablet and SD cards. You can connect it at the end of a daisy chain and expect all of the security and benefits that you would from any Thunderbolt 3 product.

6SD4FCRTB3C is TAA compliant and comes with a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Access multimedia content quickly, anywhere you go
- Ideal for creative professionals on assignment
- Creative professionals working with 4K and 3D content

Features

- Edit your photos and videos anywhere you go using this portable SD card reader
- Access up to 6 SD cards at the same time with this multi-card reader
- Power the SD card reader through the Thunderbolt 3 port on your device
- Enjoy simple connections with an integrated Thunderbolt 3 cable

Hardware	Warranty	2 Years
	Interface	Thunderbolt 3
	Bus Type	Thunderbolt 3
	Chipset ID	Intel - JHL6240
		Texas Instruments - TPS65983
		Genesys Logic - GL3226
		ASMedia - ASM1061
Performance	Maximum Data Transfer Rate	5Gbps
	Type and Rate	Thunderbolt 3 - 40 Gbit/s
	Type and Rate	UHS-II (SD 4.0; 312MB/s)
	Type and Rate	SDXC (Secure Digital eXtended Capacity)
	Memory Media Type	SDHC (Secure Digital High Capacity)
	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
Connector(s)	Drive Connectors	SD / MMC Slot
	Host Connectors	Thunderbolt 3 USB-C (24-pin) (40Gbps)
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	Note	Use the Thunderbolt 3 port on your host computer with the highest power output for the best performance. To ensure proper operations of this device a Thunderbolt 3 15W port is required. Consult the manufacturer of your host computer for details regarding the power specifications of your Thunderbolt 3 ports.

Indicators	LED Indicators	Activity
Power	Power Source	Bus Powered
Environmental	Operating Temperature	0C to 60C (32F to 140F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0~90% RH
Physical Characteristics	Color	Silver & Black
	Material	Plastic
	Cable Length	8.7 in [2.2 cm]
	Product Length	5.3 in [1.4 cm]
	Product Width	3.2 in [82.000 mm]
	Product Height	0.7 in [19.000 mm]
	Weight of Product	5.3 oz [151.000 g]
Packaging Information	Package Length	8.3 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.6 in [40.000 mm]
	Shipping (Package) Weight	9.1 oz [258.000 g]
What's in the Box	Included in Package	SD Card Reader
	Included in Package	Quick-Start Guide

**Product appearance and specifications are subject to change without notice.*

