

3m (10ft) Computer Power Cord, 18AWG, EU Schuko to C13 Power Cord, 250V 10A, Black Replacement AC Cord, TV/Monitor Power Cable, Schuko CEE 7/7 to IEC 60320 C13 Power Cord - PC Power Supply Cable

Product ID: 713E-3M-POWER-CORD



Universal Replacement for CEE 7/7 to C13 Power Cables

This replacement power cord features an EU Schuko CEE 7/7 two-pronged plug and IEC C13 female plug. It is compatible with most monitors, PCs, scanners, and printers.

High-Quality Construction

This monitor power cord is universal for all monitors that feature a C14 inlet. Built with three conductor 18 AWG wires and is rated to carry 250 V at 10 A. It is constructed with fully molded connectors with strain reliefs, ensuring reliable and durable connections for your device.

Comprehensive Product Testing and Expert-Level Technical Support

StarTech.com conducts thorough compatibility and performance testing for all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad range of product expertise. They work alongside StarTech.com Engineers to provide support pre and post-sale support.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility







Applications

Features

- AC POWER CABLE: This 3m (10ft) 18AWG flexible computer power cable with EU CEE 7/7 Plug and IEC C13 female plug is suitable for workstation/home office use Rated to carry 250V at 10A
- PERFORMANCE AND SAFETY: Fully molded ends for durability and VDE approved connectors 3 Conductor power cable made with 100% copper wire Fire Rating: VW-1
- SPECS: 3m (10ft) Power Cord EU Schuko Plug to IEC 60320 C13 Female Plug 18AWG (0.75mm) 250V 10A (Max) Jacket Rating: H05VV-F Jacket Material: PVC Color: Black Temperature Range: -10 to 35 Cable Outer Diameter: 6.8mm
- COMPATIBILITY: EU Schuko Plug works with European electrical outlets IEC C13 female plug works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware		
	Warranty	Lifetime
	Number of Conductors	3
	Cable Jacket Material	PVC
	Cable Shield Material	Nickel
	Fire Rating	VW-1 Rated
	Cable Type	SVT
Connector(s)		
	Connector A	1 - CEE 7/7 Power (European)
	Connector B	1 - IEC 60320 C13 Power
Power		
	Input Voltage	250 AC
	Input Current	10 A
Environmental		
	Operating Temperature	-10C to 35C
	Storage Temperature	-20C to 60C





Physical Characteristics

Color Black

Wire Gauge 0.75mm²

Cable Length 9.8 ft [3 m]

Product Length 1.4 in [3.6 cm]

Product Width 118.1 in [300.0 cm]

Product Height 2.0 in [5.0 cm]

Weight of Product 10.0 oz [284.0 g]

Packaging Information

Package Quantity 1

Package Length 5.5 in [14.0 cm]

Package Width 11.4 in [29.0 cm]

Package Height 2.2 in [5.5 cm]

Shipping (Package)

Weight

10.3 oz [292.0 g]

What's in the Box

Included in Package 1 - 3m Power Cord

^{*}Product appearance and specifications are subject to change without notice.