

Video Wall TV Mount for up to 70-inch and 154lb (70kg) Displays, Landscape/Portrait Orientation, Bracket with Kickstand Design, Six-Point Adjustments

Product ID: 715LPQ-TV-VIDEO-WALL



Build modular video wall installations with a TV mount that supports six points of adjustment while still providing pop-out rear access, helping simplify alignment and maintenance in professional AV setups.

Combine multiple mounts to build flexible video wall layouts like 2x2, 1x4, or custom configurations for commercial and public-facing deployments. Each wall bracket supports displays up to 70-inch and 154lb (70kg).

Install displays vertically or horizontally with VESA compatibility from 200x200 to 600x400mm, giving you greater versatility when designing video wall layouts. A wall mounting plate CAD file and instructional video are available for download to support planning and integration.

Pop-out design with a kickstand extends up to 12.8in (32.5cm) from the wall, providing easy rear access for adjustments, maintenance, and cable management on mounted TV panels.

Six adjustments provide control over height, lateral positioning, tilt, swivel, depth, and rotation, helping to fine-tune final placement without remounting the displays for alignment and a clean video wall finish.

Certifications, Reports and Compatibility

Applications

Features

- Create Scalable Video Wall Setups: Supports 45 to 70-inch displays up to 154lb (70kg), letting you combine mounts to create flexible video wall layouts like 2x2, 1x4, or other custom configurations

- **Design More Versatile Video Wall Layouts:** Mount displays in portrait or landscape orientation with VESA compatibility from 200x200 to 600x400; CAD file and instructional video are available to support planning and integration
- **Achieve Precise Screen Alignment:** Fine-tune height, lateral position, tilt, swivel, depth, and rotation with six-point adjustment making final alignment easier without remounting the displays; NOTE: 1mm thermal expansion gap required
- **Pop-Out Rear Access:** Convenient pop-out design extends up to 12.8 in (32.5 cm) from the wall, and an integrated kickstand enables fast rear-screen access for adjustments, maintenance, and cable management
- **The IT Pro's Choice:** Our TV wall mounts are tested in our Innovation Lab for reliable, long-lasting performance and stability in professional environments, from conference rooms to digital signage; Backed by free lifetime 24/5 multilingual assistance

General

UPC	065030919852
Warranty	5 Years

Physical & Environmental

Color	Black
Product Length	4.7 in [120 mm]
Product Width	25.2 in [640 mm]
Product Height	21.4 in [544 mm]
Weight of Product	370.6 oz [10500 g]

Performance

Anti-theft	Yes
Minimum Display Size	45"
Maximum Display Size	70"
Video Wall	Yes
Display Tilt	+2 / -3
Height Adjustment	Yes

Hardware

Number of Displays	1
--------------------	---

Mounting Options	Wall-Mount
Minimum Profile from Wall	5.6 in [143 mm]
VESA Hole Pattern(s)	200x200 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x400 mm

Packaging & In-the-Box

Included in Package	1 - Video Wall Mount Assembly
	2 - TV VESA Brackets, I
	2 - TV VESA Brackets, II
	1 - Lateral Adjuster, Left
	1 - Lateral Adjuster, Right
	1 - 6mm Hex Key
	4 - M6x10mm Screws
	4 - M6x14mm Screws
	4 - M6x30mm Screws
	4 - M8x16mm Screws
	4 - M8x35mm Screws
	4 - Wall Mounting Screws
	6 - Concrete Wall Anchors
	10 - Washers
	4 - Long Spacers

4 - Short Spacers

1 - Product Documentation

Package Width	22.3 in [566 mm]
Package Depth	23.0 in [585 mm]
Package Height	5.3 in [135 mm]
Shipping (Package) Weight	533.0 oz [15100 g]

****Product appearance and specifications are subject to change without notice.***