

## Refurbished 41U 29.5" Depth Enclosed Server Rack Cabinet

**Product ID:** 7230CABINETR

Refurbished units may have  
minor scratches or dents.



The 7230CABINETR Refurbished 41U 29.5" Depth Enclosed Server Rack Cabinet is a high quality, lockable and dust-reduced environment for shallow (up to 27" deep) rackmount servers and network equipment.

With exterior dimensions of H75.5" x W22" x D29.5", this sturdy space saving unit is made from extruded aluminum for an appealing appearance. A lockable smoked plexiglass front door and solid aluminum rear door provide quick access to equipment. The internal front and rear mounting rails offer adjustable depth to fit virtually any piece of equipment that is less than 27 inches deep.

A standard roof-mounted triple motor AC fan unit and high-flow air filter below the rear door provide up to 300 CFM of bottom to top air flow through the cabinet, removing the heat produced by the enclosed equipment.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

## Certifications, Reports and Compatibility



## Applications

- Data centers
- Industrial control centers
- Telecommunication closets

- Audio/Visual control centers

## Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable threaded mounting rails inside cabinet
- Front and back doors are removable and can be switched to open left or right
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- 1000 kg (2210 lbs) weight capacity
- Rolling casters provide full mobility
- Includes front flip-up stabilizers, lockable front door with 2 keys, and 50 Philips-head mounting screws
- Comes fully assembled

---

### Hardware

Warranty	None
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	41U
Fan(s)	Yes
Fans	3 - 5in
Casters	Included
Industry Standards	EIA RS310-C

---

### Performance

Weight Capacity (Stationary)	2205.0 lb [1000 kg]
Air Flow Rate	300 CFM

---

### Physical Characteristics

Color	Black
Material	Aluminum
Internal Width	19.0 in [48.3 cm]
Internal Depth	26.5 in [67.3 cm]
Product Length	29.5 in [749.3 mm]
Product Width	22.0 in [559 mm]
Product Height	75.5 in [1918 mm]

---

#### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	33.7 in [857.2 mm]
Package Width	24.8 in [629 mm]
Package Height	83.2 in [2114.5 mm]
Shipping (Package) Weight	230.0 lb [104.3 kg]

---

#### What's in the Box

Included in Package	1 - 41U Server Rack
	1 - Bag of screws, fasteners and keys

---

***\*Product appearance and specifications are subject to change without notice.***