

HPE 813874-B21 Compatible SFP+ Module - 10GBASE-T - SFP to RJ45 Cat6/Cat5e - 10GE Gigabit Ethernet SFP+ - RJ-45 30m - HPE BladeSystem, c-Class

**Product ID:** 813874B21ST



The 813874B21ST is an HPE 813874-B21 compatible copper transceiver module that has been designed, programmed and tested to work with HPE brand switches and routers. It delivers dependable 10 GbE connectivity over copper cable, for 10GBASE-T compliant networks, with a maximum distance of up to 30 m (98.4 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 10 Gbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 30 m (98.4 ft)
- MTBF: 4,598,430 hours
- Digital Diagnostics Monitoring (DDM): No

This SFP+ copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP+ modules in HP switches and routers
- Expand your network to remote segments

## Features

- **100% HPE 813874-B21 COMPATIBLE:** Works with HPE SN2010M 25GbE 18SFP28 4QSFP28 Switch, Virtual Connect Flex-10/10D Module, Flex-10/10D Module Enterprise Edition, FlexFabric 10Gb/24-Port Enterprise Edition, FlexFabric 10Gb/24-Port Module
- **TECHNICAL SPECS:** 10GBASE-T; 10Gbps; Copper; RJ-45 Connector; Distances up to 30m (98.4ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in HPE routers and switches
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Compatible Brand	HPE

---

### Performance

Maximum Data Transfer Rate	10 Gbps
Max Transfer Distance	30m [98.4ft]
Type	Copper
DDM	No
Compatible Networks	10 Gbps
MTBF	4,598,430 hours
Power Consumption (In Watts)	2.3 W (max.)

---

**Connector(s)**

Local Unit Connectors	1 - RJ-45
-----------------------	-----------

---

**Power**

Output Voltage	3.3V DC
----------------	---------

---

**Environmental**

Operating Temperature	0C ~ +70C
-----------------------	-----------

Storage Temperature	-40C ~ 90C
---------------------	------------

Humidity	95%
----------	-----

---

**Physical Characteristics**

Color	Silver
-------	--------

Product Length	2.7 in [7.0 cm]
----------------	-----------------

Product Width	0.5 in [1.3 cm]
---------------	-----------------

Product Height	0.5 in [1.4 cm]
----------------	-----------------

Weight of Product	0.9 oz [25.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	3.0 in [7.6 cm]
----------------	-----------------

Package Width	4.7 in [12.0 cm]
---------------	------------------

Package Height	1.3 in [3.4 cm]
----------------	-----------------

Shipping (Package) Weight	2.4 oz [68.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	1 - SFP+ Transceiver
---------------------	----------------------

---

*\*Product appearance and specifications are subject to change without notice.*