

6ft (1.8m) Power Extension Cord, C14 to C13 PDU Power Cord, 13A 250V, 16AWG, Black Extension Cable, AC Power Cable for PDU/Power Supply, TAA Compliant, UL Listed

Produkt-ID: 8714-6600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend a monitor, scanner, printer, or PC power cord by an additional 6 ft

Merkmale

- AC POWER CORD: 6ft (1.83m) 16AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 13A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.83m); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 16AWG; 250V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC
Feuerwiderstandssklasse	Klasse VW-1 e

Kabeltyp	SJT
Leistung	
Max. Kabellänge	6.0 ft [1.8 m]
Steckverbinder	
Steckverbinder A	1 - IEC 60320 C14 Strom
Steckverbinder B	1 - IEC 60320 C13 Strom
Strom	
Eingangsspannung	250 AC
Eingangsstrom	13A
Umgebungsbedingungen	
Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH
Physische Eigenschaften	
Farbe	Schwarz
Drahtstärke	16 AWG
Kabellänge	6.0 ft [1.8 m]
Außendurchmesser des Kabels	0.3 in [8.5 mm]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	1.1 in [2.9 cm]
Produkthöhe	0.8 in [2.1 cm]
Produktgewicht	8.5 oz [240.0 g]
Verpackungsinformationen	
Paketlänge	7.8 in [19.9 cm]

Paketbreite	3.0 in [7.6 cm]
Pakethöhe	2.2 in [5.5 cm]
Versandgewicht (Verpackung)	8.8 oz [250.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1,8m C14 auf C13 Stromkabel Verlängerung
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.