

6ft (1.8m) Power Cord Splitter, C14 to 2x C13 AC Power Cable, 10A 250V, 18AWG, AC Power Cord Splitter, PC Power Supply Cable, TAA Compliant, UL Listed

Produkt-ID: 8723-8600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Power two workstation devices from a single PDU or wall outlet
- Facilitate two power connections where connectivity is limited

Merkmale

- AC POWER CORD: 6ft (1.83m) 18AWG Computer Power Cord Y Splitter with IEC 60320 C14 to 2x IEC 60320 C13 connectors is suitable for home or office use; Split a single power cord to power two devices or dual monitors; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.83m); TAA Compliant; IEC 60320 C14 to 2x C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 connector works with North American PDUs and power cables; IEC 60320 C13 connector works with most desktop computers, servers, PDUs, printers, and more; PC power splitter cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to 2x C13 power cord Y splitter is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC
Feuerwiderstandssklasse	Klasse VW-1e
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - IEC 60320 C14 Strom
Steckverbinder B	2 - IEC 60320 C13 Strom

Strom

Eingangsspannung	250V AC
Eingangsstrom	10A
Ausgangsstrom	10A

Umgebungsbedingungen

Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	6.0 ft [1.8 m]
Außendurchmesser des Kabels	0.3 in [8.5 mm]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	2.0 in [5.1 cm]
Produkthöhe	0.6 in [1.6 cm]
Produktgewicht	12.5 oz [354.0 g]

Verpackungsinformationen

Paketlänge	10.2 in [25.8 cm]
Paketbreite	3.7 in [9.3 cm]

Pakethöhe	1.8 in [4.6 cm]
Versandgewicht (Verpackung)	12.7 oz [360.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1,8m C14 Stecker auf 2x C13 Buchse Splitterkabel
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.