

10ft (3m) Power Extension Cord, PDU Style C14 to Locking C13, PDU Power Cord, 10A 250V, 18AWG, Power Extension Cable, TAA Compliant, UL Listed

Product ID: 87L3-8A00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

• Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards

• Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS

- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility





Applications

- Locking C13 connector avoids accidental power disconnection
- Extend a monitor, scanner, printer, or PC power cord by an additional 10ft

Features

• AC POWER CORD: 10ft (3.05m) power supply extension cable with IEC 60320 C14 to Locking C13 connector is suitable for workstations or rackmount equipment; Securely connect devices to a PDU or extend a C13 power cable; Indoor use; Rated to carry 250V at 10A

• BUILT FOR PERFORMANCE AND SAFETY: UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire

• SPECS: 10ft (3.05m); TAA Compliant; IEC 60320 C14 to Locking IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)

• COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware		
	Warranty	Lifetime
	Number of Conductors	3
	Connector Plating	Nickel
	Cable Jacket Material	PVC
	Fire Rating	VW-1 Rated
	Cable Type	SJT
Connector(s)		
	Connector A	1 - IEC 60320 C14 Power
	Connector B	1 - IEC 60320 C13 Power





Power	langest Maltana	252)/ 4.0
	Input Voltage	250V AC
	Input Current	10A
Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Black
	Wire Gauge	18 AWG
	Cable Length	10.0 ft [3.0 m]
	Cable OD	0.3 in [7.8 mm]
	Product Length	10.0 ft [3.0 m]
	Product Width	1.2 in [2.9 cm]
	Product Height	0.7 in [1.7 cm]
	Weight of Product	0.0 oz [0.0 g]
Packaging Information		
	Package Length	5.5 in [14.0 cm]
	Package Width	19.3 in [49.0 cm]
	Package Height	3.1 in [8.0 cm]
	Shipping (Package) Weight	10.9 oz [310.0 g]
What's in the Box	Included in Package	1 - 10ft C14 to Locking C13 Power Extension Cord

*Product appearance and specifications are subject to change without notice.