

6ft (1.8m) Heavy Duty PDU Power Cord, C14 to C15, 15A 250V, 14AWG, Green PDU Power Cable, C14 to C15 Heavy Gauge AC Power Cord, TAA Compliant, UL Listed

Produkt-ID: 8915-4606-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Heavy Duty power cord supports high-powered equipment and PDUs

Merkmale

- **HEAVY DUTY POWER CORD:** 6ft (1.8m) 14AWG Green Heavy Duty PDU power cord with IEC 60320 C14 to IEC 60320 C15 connector is suitable for servers or high-powered equipment; Indoor use; Rated to carry 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C15; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Green; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C15 connector works with most servers, switches, and high-power rackmount appliances; Replacement PDU power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC
Feuerwiderstandssklasse	Klasse VW-1e
Kabeltyp	SJT

Steckverbinder

	Steckverbinder A	1 - IEC 60320 C14 Strom
	Steckverbinder B	1 - IEC 60320 C15 Strom
Strom	Eingangsspannung	250V AC
	Eingangsstrom	15A
	Ausgangsstrom	15A
Umgebungsbedingungen	Betriebstemperatur	-20° to 105°C (-4° to 221°F)
	Lagertemperatur	-20° to 105°C (-4° to 221°F)
	Feuchtigkeit	0% to 65% RH
Physische Eigenschaften	Farbe	Grün
	Drahtstärke	14 AWG
	Kabellänge	6.0 ft [1.8 m]
	Außendurchmesser des Kabels	0.3 in [7.8 mm]
	Produktlänge	6.0 ft [1.8 m]
	Produktbreite	1.1 in [2.9 cm]
	Produkthöhe	0.8 in [2.1 cm]
	Produktgewicht	10.6 oz [300.0 g]
Verpackungsinformationen	Paketlänge	10.4 in [26.4 cm]
	Paketbreite	4.9 in [12.5 cm]
	Pakethöhe	2.9 in [7.3 cm]
	Versandgewicht	10.7 oz [302.0 g]

(Verpackung)

Verpackungsinhalt

Im Paket enthalten

1 - 1,8 m C14 auf C15
Hochleistungs-Netzkabelverlängerung - Grün

Garantieinformationen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.