

6ft (1.8m) Heavy Duty PDU Power Cord, C14 to C15, 15A 250V, 14AWG, Orange PDU Power Cable, C14 to C15 Heavy Gauge AC Power Cord, TAA Compliant, UL Listed

Produkt-ID: 8915-460Q-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Heavy Duty power cord supports high-powered equipment and PDUs

Merkmale

- HEAVY DUTY POWER CORD: 6ft (1.8m) 14AWG Orange Heavy Duty PDU power cord with IEC 60320 C14 to IEC 60320 C15 connector is suitable for servers or high-powered equipment; Indoor use; Rated to carry 250V at 15A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C15; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Orange; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C15 connector works with most servers, switches, and high-power rackmount appliances; Replacement PDU power cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1
e

Kabeltyp SJT

Steckverbinder

Steckverbinder A 1 - IEC 60320 C14 Strom

Steckverbinder B 1 - IEC 60320 C15 Strom

Strom

Eingangsspannung 250V AC

Eingangsstrom 15A

Ausgangsstrom 15A

Umgebungsbedingungen

Betriebstemperatur -20° to 105°C (-4° to 221°F)

Lagertemperatur -20° to 105°C (-4° to 221°F)

Feuchtigkeit 0% to 65% RH

Physische Eigenschaften

Farbe Orange

Drahtstärke 14 AWG

Kabellänge 6.0 ft [1.8 m]

Außendurchmesser des Kabels 0.3 in [7.8 mm]

Produktlänge 6.0 ft [1.8 m]

Produktbreite 1.1 in [2.9 cm]

Produkthöhe 0.8 in [2.1 cm]

Produktgewicht 10.6 oz [300 g]

Verpackungsinformationen

Paketlänge 10.5 in [26.6 cm]

Paketbreite 3.5 in [9.0 cm]

Pakethöhe 1.7 in [4.4 cm]

Versandgewicht 11.1 oz [314.0 g]

(Verpackung)

Verpackungsinhalt

Im Paket enthalten	1 - 1,8 m C14 auf C15 Hochleistungs-Netzkabelverlängerung - Orange
--------------------	---

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

