

## Fiber Optic Cable - 10 Gb Aqua - Multimode Duplex 50/125 - LSZH - LC/LC - 2 m

Product ID: A50FBLCLC2



The A50FBLCLC2, 2-meter (6.6ft), 10 Gigabit, Aqua Multimode 50/125 Duplex LSZH Fiber Patch Cable is terminated at both ends with LC (male) connectors and is composed of 50/125 micron OM3 aqua fiber to deliver reliable data transfers at blinding speeds making it perfect for fiber cable runs between multiple backbone switches, hubs and routers as well as higher end networking equipment.

Suited for a broad range of environments, A50FBLCLC2 is housed in a flame retardant, LSZH (Low-Smoke, Zero-Halogen) cable jacket, taking safety to a new level by ensuring minimal smoke, toxicity and corrosion in the event of a fire – making it the best choice for a wide range of environments, including industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

### Certifications, Reports and Compatibility



### Applications

- Used in 10 Gigabit high speed network environments
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

### Features

- Designed to be used in 10 Gb Ethernet applications
- Attenuation loss meets or exceeds industry standards
- A solution that is cost effective and supports longer distances
- A more durable cable design

<b>Hrdvara</b>	Warranty	Lifetime
	Brandteknisk klass	LSZH Rated (Low Smoke Zero Halogen)
	Fiberstorlek	50/125
<b>Prestanda</b>	Maximal dataverfringshastighet	100Gbps 10Gbps / 40Gbps / 100Gbps
	Kabelklassificering	OM3
	Fiberklassificering	Multi Mode
	Fibertyp	850nm
	Vglngd	
<b>Kontakt(er)</b>	Connector A	Fiber Optic LC Duplex
	Connector B	Fiber Optic LC Duplex
<b>Milj</b>	Drifttemperatur	-20C to 60C (-4F to 140F)
	Frvaringstemperatur	-20C to 60C (-4F to 140F)
	Luftfuktighet	0~90% RH
<b>Utseende</b>	Frg	Aqua
	Kabellngd	6.6 ft [2 m]
	Diameter	3mm
	Produktlngd	6.6 ft [2 m]
	Produktvikt	1.2 oz [34 g]
<b>Frpackning</b>	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2 cm]
	Package Height	0.5 in [13 mm]
	Fraktvikt (frpackning)	1.5 oz [43 g]
<b>Vad det r i ldan</b>	Ingr i paketet	2m 10 Gb Aqua Multimode 50/125 Duplex LSZH Fiber Patch Cable LC - LC

*\*Product appearance and specifications are subject to change without notice.*