

Fiber Optic Cable - 10 Gb Aqua - Multimode Duplex 50/125 - LSZH - LC/SC - 5 m

Productcode: A50FBLCSC5



Perfect for fiber cable runs between multiple backbone switches, hubs and routers as well as higher end networking equipment, this high speed 10 Gigabit Multimode Duplex Fiber Cable is terminated with LC and SC connectors, and is composed of 50/125 micron OM3 aqua fiber to deliver reliable data transfers at blinding speeds.

Suited for a broad range of environments, A50FBLCSC5 is housed in a flame retardant, LSZH (Low-Smoke, Zero-Halogen) cable jacket, taking safety to a new level by ensuring minimal smoke, toxicity and corrosion in the event of a fire – making it the best choice for a wide range of environments, including industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

## Certificaties, rapporten en compatibiliteit

### Toepassingen

- Used in 10 Gigabit high speed network environments
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

### Eigenschappen



- Designed to be used in 10 Gb Ethernet applications
- Attenuation loss meets or exceeds industry standards
- A solution that is cost effective and supports longer distances
- A more durable cable design

---

#### Hardware

Garantiebeleid	Lifetime
Brandbestendigheid	LSZH-rating (weinig rook, geen halogeen)
Glasvezelformaat	50/125

---

#### Prestaties

Maximale overdrachtsnelheid	100 Gbps
Kabelspecificatie	10Gbps / 40Gbps / 100Gbps
Glasvezelclassificatie	OM3
Glasvezeltype	Multi-Mode
Golflengte	850nm

---

#### Connector(en)

Connector A	Glasvezel LC duplex
Connector B	Glasvezel SC duplex

---

#### Gebruiksomgeving

Bedrijfstemperatuur	-20°C to 60°C (-4°F to 140°F)
Opslagtemperatuur	-20°C to 60°C (-4°F to 140°F)
Vochtigheid	0% - 90% rel. luchtvochtigheid

---

#### Fysieke eigenschappen

Kleur	Aqua
Kabellengte	16.4 ft [5 m]



Diameter	3mm
Lengte product	16.4 ft [5 m]
Gewicht product	2.7 oz [77 g]

---

Verpakkingsinformatie

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.8 in [21 mm]
Verzendgewicht (verpakt)	3.0 oz [86 g]

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

