

120mm Axial Rack Muffin Fan for Server Cabinet, 115V, AC Cooling, Low Noise & Quiet PC Computer Case Fan

Produkt-ID: ACFANKIT12



The ACFANKIT12 12cm AC Fan Kit for Server Racks and Cabinets can be installed in StarTech.com's Wall mountable Server Rack Cabinets (RK12WALHM, RK1219WALL and RK1219WALH), as well as many full sized racks from StarTech.com and other manufacturers.

This powerful, yet quiet ball bearing fan will help increase airflow and reduce heat build-up within the cabinet. Capable of moving 107 CFM of air through the rack, this AC powered fan kit is sure to prolong the life of your rackmount equipment.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Increase airflow, and reduce heat around rack mounted hardware

Merkmale

- **QUIET VENTILATION:** Increase airflow in your server rack / cabinet to extend equipment life; This 4.7in / 120mm axial rack muffin fan provides low noise (45.7 dbA), AC cooling and is ideal for use with your server, AV and computer equipment

- **POWERED COOLING SYSTEM:** This high performance computer and server rack fan has a standard AC power connection with included power cord, making it a simple, convenient addition to existing racks or cabinets in your home or office
- **BUILT TO LAST:** Built with a solid metal frame, this fan is 120mm x 38mm and delivers a 107 CFM airflow rate for optimal performance; Operating temperature of 14°F to 158°F (-10°C to 70°C), making it ideal for most environments
- **VERSATILE FAN KIT:** Designed to provide airflow and help to reduce heat build-up, this 115V muffin fan is great for computer cases or rack mounted equipment; It comes with the fan, power cord, screws, nuts and washers so you're ready for installation
- **THE IT PRO's CHOICE:** Designed and built for IT Professionals, this rack fan is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen 2 Years

Lüfterlagertyp Kugellager

Leistung

Luftzirkulationsrate 107 CFM

Geräuschpegel 47.5 dBA

Lüfterdrehzahl 3050

Strom

Eingangsspannung 115V AC

Stromverbrauch 20

Umgebungsbedingungen

Betriebstemperatur -10°C to 70°C (14°F to 158°F)

Physische Eigenschaften

Farbe Schwarz

Gehäusotyp Aluminium

Produktlänge 4.7 in [12 cm]

Produktbreite 1.5 in [3.8 cm]

Produkthöhe	4.7 in [12 cm]
Produktgewicht	20.6 oz [583.8 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	5.8 in [14.8 cm]
Paketbreite	7.7 in [19.5 cm]
Pakethöhe	1.9 in [4.8 cm]
Versandgewicht (Verpackung)	1.4 lb [0.6 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 120mm x 120mm x 38mm Fan
	4 - 8-32 Zinc Plated MachineScrew Nut
	4 - 8-32 x 2" Phillips Pan HeadZinc Plated Machine ScrewBulk
	4 - #8 Zinc Plated Split LockWasher
	1 - AC Power Cord

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.