

12cm AC Fan Kit for Server Rack Cabinet

Product ID: ACFANKIT12



The ACFANKIT12 12cm AC Fan Kit for Server Racks and Cabinets can be installed in StarTech.com's Wall mountable Server Rack Cabinets (RK12WALHM, RK1219WALL and RK1219WALH), as well as many full sized racks from StarTech.com and other manufacturers.

This powerful, yet quiet ball bearing fan will help increase airflow and reduce heat build-up within the cabinet. Capable of moving 107 CFM of air through the rack, this AC powered fan kit is sure to prolong the life of your rackmount equipment.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Increase airflow, and reduce heat around rack mounted hardware

Features

- Standard AC Power connection
- Removable 115V plug for use with direct current
- Solid metal frame and sturdy design

Hardware

Warranty	2 Years
Fan Bearing Type	Ball Bearing

Performance

Air Flow Rate	107 CFM
Noise Level	47.5 dBA
Fan RPM	3050

Power

Input Voltage	115V AC
---------------	---------

Environmental

Operating Temperature	-10C to 70C (14F to 158F)
-----------------------	---------------------------

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.7 in [12 cm]
Product Width	1.5 in [38 mm]
Product Height	4.7 in [12 cm]
Weight of Product	20.6 oz [583.8 g]

Packaging Information

Package Length	7.8 in [19.7 cm]
Package Width	7.7 in [19.5 cm]
Package Height	1.5 in [38 mm]
Shipping (Package) Weight	21.9 oz [619.6 g]

What's in the Box

Included in Package	120mm x 120mm x 38mm Fan
	8-32 Zinc Plated MachineScrew Nut
	8-32 x 2" Phillips Pan HeadZinc Plated Machine ScrewBulk



#8 Zinc Plated Split LockWasher

AC Power Cord

****Product appearance and specifications are subject to change without notice.***

