

1U Adjustable Mounting Depth Vented Rack Mount Shelf - 175lbs / 80kg

Product ID: ADJSHELF



The ADJSHELF Adjustable Mounting Depth Rack Mount Shelf offers a simple way to effectively organize mission critical computer hardware in your server racks and cabinets.

Compatible with all 19in (wide) server racks/cabinets, the fixed rack shelf can be adjusted from 19in to 38in (mount depth) as necessary. A sturdy cold-rolled steel construction provides long term durability and enables a weight capacity of up to 175 lbs (80 kg).

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware.

Features

- Low cost adjustable shelf for most 19 inch wide cabinets and racks
- Vented shelf plate to preserve airflow
- Weight capacity up to 175 lbs (80 kg)
- adjustable mounting depth of 19" -38"

- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
U Height	1U
Cable Management	No

Performance

Weight Capacity (Stationary)	176.8 lb [80 kg]
------------------------------	------------------

Special Notes / Requirements

Note	Depth adjustable from 19-38"
------	------------------------------

Physical Characteristics

Color	Black
Internal Width	17.6 in [44.6 cm]
Internal Height	1.6 in [40 mm]
Internal Depth	27.6 in [70 cm]
Product Length	27.6 in [70 cm]
Product Width	17.5 in [44.5 cm]
Product Height	1.6 in [40 mm]
Weight of Product	9.8 lb [4.4 kg]
Maximum Mounting Depth	38.3 in [97.4 cm]
Minimum Mounting Depth	19.5 in [49.5 cm]

Packaging Information

Package Length	28.7 in [73 cm]
Package Width	20.5 in [52 cm]
Package Height	2.6 in [65 mm]



Shipping (Package) Weight	12.2 lb [5.5 kg]
------------------------------	------------------

**What's in the
Box**

Included in Package	slotted fixed shelf
	M5 screws
	M5 cage nuts
	instruction manual
	front mounting brackets
	rear mounting brackets
	M5 flanged lock nuts
	M5 truss head screws

****Product appearance and specifications are subject to change without notice.***

