

1-Port Gigabit PoE+ Injector, 10M/100M/1G Ethernet, PoE/PoE+ (802.3af/802.3at), 30W Power Budget, Wall Mountable, Unmanaged Inline Power Over Ethernet - TAA

Produkt-ID: AF211C-POE-INJECTOR




This 1-port multi-speed PoE+ Injector serves as a Power Sourcing Equipment (PSE) device and enables Ethernet speeds of 10Mbps, 100Mbps, and 1Gbps. This TAA-compliant mid-span inline injector can transmit network data and power up to 328ft (100m) for remote Powered Devices (PD).

Single port PoE injector supports the IEEE 802.3af and 802.3at PSE standards, and delivers up to 30W output (54V DC, 0.6A). This enables seamless data and power transmission over Cat5/5e/6/6a to remote Powered Devices (PD) such as IP cameras, access control devices, remote kiosks (POSs), wireless access points (APs), PoE lighting, and digital signage. A built-in LAN Transformer reduces EMI to maintain strong, reliable signal strength across different environments.

All Ethernet cables can be routed from one side of the unit for efficient and organized cable management. The compact design (4x2.3x1.3-inch-100x58.4x33.4 mm) ensures straightforward integration into existing network infrastructure, saving space and time during installation.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **GIGABIT POE INJECTOR:** Single port PoE+ injector supports up to 1Gbps with auto-negotiation; TAA-compliant Power Sourcing Equipment (PSE) supports up to 30W PoE/PoE+; Features level-4 ESD protection for reliable performance and durability
- **MULTIPLE SPEEDS:** Auto-negotiation between 1Gbps & 10/100Mbps Ethernet; Deliver data & power to Powered Devices (PDs) up to 328ft (100m) w/Cat5/5e/6/6a cabling; Unmanaged inline injector w/built-in LAN transformer for electrical isolation reducing EMI
- **HASSLE-FREE INSTALLATION:** Wall-mountable design with front mounting holes; Streamline deployment without additional software/settings; Connect the PoE injector to the network (e.g., switch or router) & the remote PD via standard Cat5/e or Cat6/6a cabling
- **APPLICATIONS:** Enable data & power over a single RJ45 connection to critical PoE devices such as IP cameras & Access Points (APs); Ideal for remote device installations with limited power sources; Wall-mountable design for convenient installation & access
- **TECH SPECS:** x2 RJ45 ports (data/data+power); 54VDC 0.6A output; 30W max output; Compliant with IEEE 802.3af and IEEE 802.3at; 10/100Mbps & 1Gbps with auto negotiation; WoL/PXE/9K jumbo frames; Wall mountable; Dimensions 4x2.3x1.3-inch (100x58.4x33.4mm)

Hardware

Garantiebestimmungen	2 Years
Ports	1
Industrienormen	IEEE 802.3at Type 2 / PoE+ (30 W) IEEE 802.3af Type 1 / PoE (15.4 W) IEEE 802.3ab (1000BASE-T) IEEE 802.3u (100BASE-TX) IEEE 802.3i (10BASE-T) IEC 61000-4-2 Level-4 ESD protection (8kV contact/15kV air)
Chipset-ID	Monolithic Power Systems - MP3924

Leistung

Wake On Lan	Ja
Max. Datenübertragungsrate	1000 Mbit/s

Max. Kabellänge	328.0 ft [100 m]
ESD Protection	+/-8kV (Contact) +/-15kV (Air)
Kompatible Netzwerke	10/100/1000 Mbps
Auto MDIX	Ja
PXE	Ja
Jumbo Frame Support	9K max.
Unterstützte Protokolle	Wake-on-LAN (WoL)

Steckverbinder

Steckverbinder A	1 - RJ-45 (PoE+)
Steckverbinder B	1 - RJ-45
Externe Ports	1 - IEC 60320 C6

Software

Betriebssystemkompatibilität	No drivers or software required
------------------------------	---------------------------------

Anzeiger

LED-Anzeiger	1 - Power LED: , Steady Green - Power is being supplied to the PoE Injector , Off - No power is being supplied to the PoE Injector
--------------	--

Strom

Stromversorgung	Standard 120V Power Cords
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.8 A
Ausgangsspannung	54 DC
Ausgangsstrom	0.6 A
Stromverbrauch	32.4

Umgebungsbedingungen

Betriebstemperatur	32°F to 122°F (0°C to 50°C)
Lagertemperatur	14°F to 158°F (-10°C to 70°C)
Feuchtigkeit	5~95% RH (Non-Condensing)

Physische Eigenschaften

Farbe	Schwarz
Gehäusetyp	Kunststoff
Produktlänge	3.9 in [10.0 cm]
Produktbreite	2.3 in [5.8 cm]
Produkthöhe	1.3 in [3.3 cm]
Produktgewicht	3.5 oz [100.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	4.9 in [12.5 cm]
Paketbreite	8.3 in [21.2 cm]
Pakethöhe	2.0 in [5.2 cm]
Versandgewicht (Verpackung)	13.1 oz [372.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - PoE-Injektor
	1 - 6ft (1.8m) NA Power Cord
	1 - Kurzanleitung

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

