

Dell EMC AOC-SFP-10G-3M Compatible 3m/9.84ft 10G SFP+ to SFP+ AOC Cable - 10GbE SFP+ Active Optical Fiber - 10Gbps SFP Plus/Mini GBIC/Transceiver Module Cable -

Product ID: AOCSFP10G3ME



The AOCSFP10G3ME is a Dell EMC AOC-SFP-10G-3M compatible fiber optical SFP+ cable that is designed, programmed and tested to work with Dell EMC brand 10 Gb compatible servers or routers and complies with MSA industry standards.

This active optical SFP+ cable (AOC) supports 10GbE applications connected through SFP+ (Mini-GBIC) ports and is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions. The AOC cable is lighter and more flexible than SFP+ direct-attach cables which makes it ideal for installation in tight spaces and over longer distances.

Designed for high-speed interconnects, this low-power, low-latency optical cable is ideal for applications such as point-to-point in-rack and across-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- Dell EMC AOC-SFP-10G-3M COMPATIBLE ACTIVE OPTICAL CABLE (AOC): Works with Dell EMC switches like , and others
- TECHNICAL SPECS: 3m Active Optical Cable 10Gbps Active Optical Fiber 2x SFP+ Pluggable Connector PVC

Cable Jacket Hot swappable MSA Compliant

- **DESIGNED FOR SERVER ROOMS:** A convenient alternative to transceivers inside and between racks. Factory termination means high performance & reliability, with less maintenance
- **OUTSTANDING SUPPORT:** Backed for life by StarTech.com for the life of the module itself, not your equipment; our cables won't void your OEM warranty and supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	Dell EMC
Cable Type	Active Optical Cable

Performance

Maximum Data Transfer Rate	10.00 Gbps
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	19,083,969 hours
Power Consumption (In Watts)	< 1.2W

Connector(s)

Connector A	SFP+
Connector B	SFP+

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	0~85% RH

Physical



Characteristics

Product Length	9.8 ft [3.0 m]
Product Width	0.6 in [14 mm]
Product Height	0.5 in [12 mm]
Weight of Product	2.3 oz [64 g]

Packaging Information

Package Length	12.8 in [32.4 cm]
Package Width	9.7 in [24.7 cm]
Package Height	3.9 in [100 mm]
Shipping (Package) Weight	3.2 oz [90 g]

What's in the Box

Included in Package	SFP+ Cable
---------------------	------------

****Product appearance and specifications are subject to change without notice.***

