

Monitor Mount Adapter for Apple iMac, iMac Pro, Cinema & Thunderbolt Displays - Only for StarTech.com Premium Mounts - Apple Computer Monitor Bracket Kit - Silver

Product ID: APLVESAMNTP



Save space with this premium VESA monitor mount adapter, by connecting your display to one of our premium monitor mounts.

Use the monitor stand adapter to mount your VESA mount monitor (75x75, 100x100) up to 34". You can also mount your Apple Cinema Display, 24-inch iMac or 27-inch iMac Pro, or Thunderbolt Display that came with a removable stand or built-in mount VESA adapter. The attractive silver finish complements Apple products.

The computer monitor mount adapter makes it easy to change your screen position, so you can work more comfortably. It can rotate your display 360 and tilts freely +90/ -15.

The VESA pole mount adapter features thumb screws for easy installation on VESA displays. Tools are also included for attaching Apple iMacs, Cinema Displays, or Thunderbolt displays to the mount. The snap-and-click design is fully compatible with the following ergonomic display mounts: ARMDUAL30, ARMDUALPS, ARMPIVOT, ARMQUADPS, ARMWALLDS2, ARMWALLDSLIP, WALLSTSI1, WALLSTSI2.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The APLVESAMNTP is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount your VESA mount display, iMac Pro, Apple Cinema and Thunderbolt Displays to a monitor arm

- This product's attractive silver finish, along with the other StarTech.com premium mounts are ideal for customer-facing environments such as waiting rooms, lobbies, retail

Features

- **APPLE DISPLAY COMPATIBLE:** Retrofit your StarTech.com premium aluminum display mounts & arms to support your iMac, iMac Pro, Apple Cinema & Thunderbolt displays with easy snap-and-click installation
- **COMPATIBILITY:** Apple monitor mount adapter only works with the StarTech.com line of premium monitor mounts (ARMDUAL30, ARMPIVOT, ARMDUALPS, ARMPIVSTND, ARMQUADPS, ARMPIVOTB2, ARMWALLDSLP, ARMWALLDS2)
- **WIDE RANGE OF MOTION:** +90/-15 vertical tilt, +/-180 horizontal swivel and 360 display rotation; height adjustable if the computer monitor mount is enabled with this feature
- **DUAL PURPOSE MONITOR BRACKET KIT:** Use as Apple monitor mount bracket or universal VESA 75x75/100x100mm compatible monitor mount adapter designed for use w/ StarTech.com premium monitor mounts & arms
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This monitor mount adapter is backed for 10 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	10 Years
# of Displays Supported	1
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Display Rotation	360

Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved
------	---

and ultrawide displays, with a max weight of 30.9 lb. (14 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 26" (66 cm).

Physical Characteristics

Color	Silver
Material	Steel
Product Length	4.7 in [12.0 cm]
Product Width	4.7 in [12.0 cm]
Product Height	3.3 in [85.0 mm]
Weight of Product	20.3 oz [575.0 g]

Packaging Information

Package Length	4.9 in [12.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	3.5 in [90.0 mm]
Shipping (Package) Weight	22.9 oz [650.0 g]

What's in the Box

Included in Package	VESA Mount
	Flange
	Access Card
	Plastic Caps
	Thumb Screws
	Torx Tool
	3mm Hex Key
	4mm Hex Key
	M6 x 16mm Screws
	User Manual



****Product appearance and specifications are subject to change without notice.***

