

Arista Networks SFP-10G-SRL Compatible SFP+ Module - 10GBASE-SR - 10GbE Multimode Fiber MMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 100m - 850nm - DDM

Product ID: AR-SFP-10G-SRL-ST



The AR-SFP-10G-SRL-ST is an Arista Networks SFP-10G-SR compatible fiber transceiver module that has been designed, programmed and tested to work with Arista Networks brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-SR compliant networks, with a maximum distance of up to 300 m (984 ft).

Technical Specifications:

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 498,745,585 hours
- Power Consumption: Low power consumption
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% ARISTA NETWORKS SFP-10G-SRL COMPATIBLE SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible Arista Networks switches and routers to deliver dependable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-SR 10Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Arista Networks routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

| | |
|--------------------|-------------------------|
| Warranty | Lifetime |
| Compatible Brand | Arista Networks |
| Industry Standards | IEEE 802.3ae 10GBASE-SR |

Performance

| | |
|----------------------------|-------------------|
| Maximum Data Transfer Rate | 10.00 Gbps |
| Max Transfer Distance | 100 m (328 ft) |
| Type | Multi Mode |
| Wavelength | 850nm |
| Fiber Operating Mode | Full-Duplex |
| DDM | Yes |
| Compatible Networks | 10 Gbps |
| MTBF | 498,745,585 hours |



**Physical
Characteristics**

| | |
|-------------------|------------------|
| Product Length | 0.5 in [13.9 mm] |
| Product Width | 2.3 in [58.4 mm] |
| Product Height | 0.5 in [12.6 mm] |
| Weight of Product | 0.7 oz [20 g] |

**Packaging
Information**

| | |
|------------------------------|------------------|
| Package Length | 4.5 in [11.5 cm] |
| Package Width | 3.5 in [90 mm] |
| Package Height | 1.2 in [31 mm] |
| Shipping (Package) Weight | 1.8 oz [50 g] |

**What's in the
Box**

| | |
|---------------------|------------------|
| Included in Package | SFP+ Transceiver |
|---------------------|------------------|

****Product appearance and specifications are subject to change without notice.***

