

Desk-mount Dual-Monitor Arm - Cross Bar - Grommet/Desk Clamp Mount

Product ID: ARMBARDUOG



This desk mount dual-monitor arm lets you mount two 13" to 27" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable dual-arm design, the double-monitor mount lets you create more usable work space by mounting your monitors side by side on a single base. The screen mount features a flat low-profile back that lets you position your displays against a wall or cubicle wall.

The computer monitor desk mount features adjustable height along the pole. The smooth +/- 30° tilt motion and +/- 30° swivel make it easy to find the optimal viewing angle. You can also rotate your display 360° for portrait or landscape viewing, and make sure your displays are perfectly aligned using the micro-adjustment knob.

The dual-monitor arm is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

Adding two monitors gives you the extra screen space you need to simplify multitasking and maximize your productivity.

ARMBARDUOG is backed by a 5-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount two monitors on a single base to save desk space

- Maximize office space, creating a dual-monitor workstation against a wall or cubicle wall
- Works with sit-stand workstations, using the desk clamp or grommet mount

Features

- Save space by mounting two monitors up to 27" onto a single base (max. weight 17.6 lb. / 8 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 23"/58.4 cm)
- Work comfortably with adjustable height, +/- 30tilt, +/- 30swivel and 360 rotation
- Versatile use with desk-clamp or grommet-hole mounting
- Place monitors close to a wall/cubicle wall, with a low-profile design

Hardware	Warranty	5 Years
	Wallmountable	No
	Cable Management	Yes
	Articulating	No
	# of Displays Supported	2
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)
Performance	General Specifications	Pole Height: 14.2" (360 mm)
	General Specifications	Dual-Arm Span: 32.87" (835 mm)
	Weight Capacity (Per Display)	17.7 lb [8 kg]
	Minimum Display Size	13"
	Maximum Display Size	27in
	Height Adjustment	Yes
	Maximum Height	14.3 in [3.6 cm]
	Display Tilt	+ 30 / - 30
	Swivel / Pivot	+30/ -30
	Display Rotation	360
Physical Characteristics	Color	Black

Material	Steel, Aluminum and Plastic
Product Length	34.3 in [8.7 cm]
Product Width	5.3 in [1.4 cm]
Product Height	20.3 in [5.2 cm]
Weight of Product	10.8 lb [4.9 kg]

Packaging Information	Package Length	18.8 in [4.8 cm]
	Package Width	9.8 in [2.5 cm]
	Package Height	4.7 in [1.2 cm]
	Shipping (Package) Weight	12.5 lb [5.6 kg]

What's in the Box	Included in Package	Column
	Included in Package	VESA Adapters
	Included in Package	Cable-Management Clips (Column)
	Included in Package	Monitor Arms
	Included in Package	End Caps
	Included in Package	Cable-Management Clips (Monitor Arm)
	Included in Package	End-Cap Screws
	Included in Package	Desk-Mount Clamp
	Included in Package	Hex Key
	Included in Package	Hex Key Screwdriver
	Included in Package	M4x14 Screws
	Included in Package	M5x14 Screws
	Included in Package	Flat Washers
	Included in Package	Grommet-Mounting Adapter
	Included in Package	Rubber Pads
	Included in Package	Instruction Manual
	Included in Package	Grommet-Mount Plate

****Product appearance and specifications are subject to change without notice.***

