

## Desk-Mount Dual Monitor Arm - Articulating

**Product ID:** ARMDUAL



StarTech.com

Enhance productivity while freeing up space. This desk mount dual monitor arm lets you mount two VESA (75x75, 100x100) displays to your desk or table, with extension, tilt, pan, swivel, pivot and height adjustments.

The dual articulating monitor arms offer a wide range of motion on several axes, giving you the freedom to place your displays side-by-side and adjust the viewing angle. Tilt your monitors +/-90 degrees and pan +/-90 degrees for ideal viewing. For viewing longer pages or blocks of code without scrolling, the dual monitor arm also supports landscape to portrait display rotation for either monitor.

Mounting your displays on a dual monitor arm above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment. Work in comfort, and reclaim valuable workspace on your desk or table.

The dual monitor mount supports two VESA mount (75x75, 100x100) displays up to 24", with a maximum weight capacity of 30lbs (13.6kg) per arm. The computer monitor mount holds your displays with ease, and integrates a cable management channel to keep things neat.

For added installation flexibility, the included mounting hardware can either clamp to the side of your desk / table or mount through a grommet hole, for a versatile dual-monitor mounting solution.

ARMDUAL is backed by a StarTech.com 5-year warranty and free, lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Mount two displays to your desk or table, using the desk clamp or grommet hole mount
- Set up two displays with easy adjustment for multi-user workstations

- Rotate displays to portrait orientation for web design and coding

## Features

- Mount two 12" to 24" displays (max weight of 30.0 lb./13.6 kg per display)
- Dual articulating arms provide a wide range of motion
- 360 rotation around the support pole and at the elbow, 180 rotation at the shoulder
- Landscape to portrait screen rotation, plus +/-90 degrees tilt and +/-90 degrees pan
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 29.2"/74.1 cm)

---

### Hardware

Warranty	5 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Mount Hole Size: 0.39 - 2.75 in. (10 - 70 mm)

---

### Performance

Weight Capacity (Per Display)	30.0 lb [13.6 kg]
Maximum Display Size	24in
Height Adjustment	Yes
Maximum Arm Extension	17.5 in [44.5 cm]
Display Tilt	+90 / - 90



Display Swivel	+90 / - 90
Swivel / Pivot	360 around the support post 180 at the shoulder 360 at the elbow
Display Rotation	360

---

**Physical Characteristics**

Color	Black
Material	Steel and Plastic
Product Length	3.0 in [75.0 mm]
Product Width	32.8 in [83.4 cm]
Product Height	12.9 in [32.7 cm]
Weight of Product	8.9 lb [4.0 kg]

---

**Packaging Information**

Package Length	22.8 in [58.0 cm]
Package Width	12.8 in [32.5 cm]
Package Height	6.3 in [16.0 cm]
Shipping (Package) Weight	10.8 lb [4.9 kg]

---

**What's in the Box**

Included in Package	Articulating LCD Arms
	Desk Clamp
	DEK
	Cover Plates
	Spacers
	M4x12mm Phillips Screws
	M4x25mm Phillips Screws



M6x12mm Phillips Screws

M6 Washers

Cable Clip

Plastic Gasket Cushions

2.5mm Allen Wrench

4mm Allen Wrench

6mm Allen Wrench

Instruction Manual

Grommet Plate

---

***\*Product appearance and specifications are subject to change without notice.***

