

Desk Mount Dual Monitor Arm – Premium Articulating Multi-Monitor Desktop VESA Mount up to 27” Displays – Adjustable Height/Rotating/Swivel/Tilt - Desk Clamp/Grommet - Silver

Product ID: ARMDUALPS



Create an ergonomic workspace with this premium desk-mount dual monitor arm, for monitors up to 27" each. The two articulating monitor arms with dual-swivel action offer a wide range of motion side to side. The attractive silver finish enhances the aesthetics of your workspace.

The dual articulating monitor arms offer a wide range of motion on several axes. It provides effortless motion to adjust the position of your monitors.

The robust aluminum design provides stable support for your monitors. The computer-monitor desk mount supports two VESA mount monitors (75x75, 100x100) with a weight capacity of up to 22 lb. (10 kg) per display. The cable-management channel helps to keep your workstation neat and tidy.

Share your screen with ease. The double monitor mount offers a full +180-degree / -180-degree pan, to move your screen left or right. It tilts freely +90 / -15 degrees to adjust the angle up or down. Rotate your screens for landscape or portrait viewing.

Work in comfort. This height-adjustable monitor mount lets you raise or lower the monitor arms along the pole, with a range of up to 6.3" (160 mm)

The fully assembled desk clamp and pole, plus quick slide-and-click connections, ensure easy assembly. It also saves time when setting up multiple units. The dual-screen mount gives you the option of desk clamp or grommet hole mounting (hardware included).

The TAA compliant ARMDUALPS is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount dual displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your displays for dual-screen access in a media room
- Spread displays apart or position them back to back for multi-user workstations
- Rotate displays to portrait orientation for web design and coding

Features

- **HEAVY DUTY MONITOR MOUNT:** VESA 75x75/100x100mm compatible dual monitor arm supports two large displays up to 27" (22lbs) per screen; Horizontal articulating & height adjustable desk/grommet hole clamp
- **EASY INSTALLATION:** Premium dual monitor arm w/ convenient toolless slide & click design makes assembling the monitor arms & VESA adapters easy, reducing set-up time; Pre-assembled desk clamp & pole
- **WIDE RANGE OF MOTION:** Ergonomic monitor mount w/ +90/-15 tilt, +/-180 swivel, 360 portrait/landscape rotating, adjustable height range of 6.3" (16cm) along pole; Back-to-back screen setup possible
- **ORGANIZED WORKSPACE:** Desktop double monitor mount w/ cable management clips along the silver arms & center pole to organize cables & hold incl. articulation tension adjustment tool for a tidy setup
- **APPLE DISPLAY COMPATIBILITY:** Snap & click accessory for StarTech.com premium mounts (APLVESAMNTP sold separately) lets you mount non-VESA monitors incl iMac/iMac Pro/Apple Cinema/Thunderbolt displays

Prominence

Warranty	10 Years
Description CDW 75 - 1st Line	StarTech.com Desk Mount Dual Monitor Arm – Premium Articulating Mount 27"

Hardware

Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

Performance

Weight Capacity (Per Display)	22.1 lb [10 kg]
Minimum Display Size	13"
Maximum Display Size	27in
Maximum Arm Extension	16.5 in [42 cm]
Maximum Arm Span	37.0 in [94 cm]
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Display Rotation	360

Physical Characteristics

Color	Silver
Material	Aluminum
Product Length	8.7 in [22.0 cm]
Product Width	7.5 in [19.0 cm]
Product Height	20.5 in [52.0 cm]
Weight of Product	9.9 lb [4.5 kg]

Packaging Information

Package Length	12.6 in [32.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	18.3 in [46.5 cm]
Shipping (Package) Weight	12.2 lb [5.5 kg]

What's in the Box

Included in Package	Swivel Arms
	VESA Monitor Mounts



Shoulder

Desk Clamp and Pole Assembly

M3 Hex Keys

EVA Cushion

Thumbscrews

Cable-Management Clip

User Manual

****Product appearance and specifications are subject to change without notice.***

