

Desk Mount Dual Monitor Arm - Premium Articulating Monitor Arm - up to 27" (17.6lb/8kg) VESA Mount Displays - Height Adjustable Monitor Mount - Rotate/Tilt/Swivel - Clamp/Grommet - Silver - TAA

Product ID: ARMDUALPS



Create an ergonomic workspace with this premium desk-mount dual monitor arm, for monitors up to 30" each. The two articulating monitor arms with dual-swivel action offer a wide range of motion side to side. The attractive silver finish enhances the aesthetics of your workspace.

The dual articulating monitor arms offer a wide range of motion on several axes. It provides effortless motion to adjust the position of your monitors.

The robust aluminum design provides stable support for your monitors. The computer-monitor desk mount supports two VESA mount monitors (75x75, 100x100) with a weight capacity of up to 22 lb. (10 kg) per display. The cable-management channel helps to keep your workstation neat and tidy.

Share your screen with ease. The double monitor mount offers a full +180-degree / -180-degree pan, to move your screen left or right. It tilts freely +90 / -15 degrees to adjust the angle up or down. Rotate your screens for landscape or portrait viewing.

Work in comfort. This height-adjustable monitor mount lets you raise or lower the monitor arms along the pole, with a range of up to 6.3" (160 mm)

The fully assembled desk clamp and pole, plus quick slide-and-click connections, ensure easy assembly. It also saves time when setting up multiple units. The dual-screen mount gives you the option of desk clamp or grommet hole mounting (hardware included).

The TAA compliant ARMDUALPS is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount dual displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your displays for dual-screen access in a media room
- Spread displays apart or position them back to back for multi-user workstations
- Rotate displays to portrait orientation for web design and coding

Features

- **HEAVY DUTY MONITOR MOUNT:** VESA 75x75/100x100mm compatible desk mount dual monitor arm supports two large displays up to 30" (22lbs) per screen; Horizontal articulating & height adjustable; desk clamp/grommet hole mount
- **EASY INSTALLATION:** Premium dual articulating monitor arm with convenient toolless slide & click design makes assembling the monitor arms & VESA adapters easy, reducing set-up time; Pre-assembled desk clamp & pole
- **WIDE RANGE OF MOTION:** Ergonomic monitor mount with +90/-15 tilt, +/-180 swivel, 360 portrait/landscape rotating, adjustable height range of 6.3" (16cm) along pole; Back-to-back computer screen setup possible
- **ORGANIZED WORKSPACE:** Universal multi monitor mount with cable management clips along the arms & center pole to organize cables & hold incl. articulation tension adjustment tool for a tidy setup at your desktop computer/PC workspace
- **APPLE DISPLAY COMPATIBILITY:** Snap & click accessory for StarTech.com premium mounts (APLVESAMNTP sold separately) lets you mount non-VESA monitors incl iMac/iMac Pro/Apple Cinema/Thunderbolt displays to this silver monitor arm

Hardware

Warranty	10 Years
Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm)
	Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm)
	Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

Performance

Weight Capacity (Per Display)	22.0 lb [10 kg]
Minimum Display Size	13"
Maximum Display Size	27"
Maximum Arm Extension	16.5 in [420 mm]
Maximum Arm Span	37.0 in [940 mm]
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Display Rotation	360

Physical Characteristics

Color	Silver
Material	Aluminum
Product Length	8.7 in [220.0 mm]
Product Width	7.5 in [19.0 cm]
Product Height	20.5 in [52.0 cm]
Weight of Product	158.2 oz [4482.0 g]

Packaging Information

Package Quantity	1
Package Length	12.9 in [32.8 cm]
Package Width	18.7 in [47.5 cm]
Package Height	5.9 in [15.0 cm]
Shipping (Package)	11.8 lb [5.4 kg]

Weight

What's in the Box

Included in Package	4 - Swivel Arms
	2 - VESA Monitor Mounts
	1 - Shoulder
	1 - Desk Clamp and Pole Assembly
	2 - M3 Hex Keys
	1 - EVA Cushion
	8 - Thumbscrews
	1 - Cable-Management Clip
	1 - User Manual

Warranty Information

Warranty	10 Years
----------	----------

**Product appearance and specifications are subject to change without notice.*