

Dual Monitor Stand - Ergonomic Desktop Monitor Stand for up to 32" (17.6lb/8kg) VESA Displays - Free-Standing Articulating Universal Computer Monitor Mount - Adjustable Height - Silver

**Product ID:** ARMDUALSS



Customize your workstation, and free up space, with this dual-monitor stand. Mount two monitors on the dual articulating monitor arms, and adjust your displays for optimum viewing with a wide range of motion. The free-standing base gives you flexibility in placing your setup within your workspace.

Work more efficiently with a dual-monitor setup. The horizontal dual-monitor stand lets you mount two VESA mount (75x75, 100x100 mm) monitors, up to 32", with a maximum weight capacity of up to 17.6 lb./8 kg per display.

Mounting your displays on a dual-monitor stand above the desk surface enables you to adjust your display height, position and viewing angles for an ergonomic workspace. The swiveling arms provide maximum viewing flexibility, letting you work in comfort.

It's easy to customize your setup, placing your monitors at the ideal height. Simply adjust the display height along the 16.7" (42.4 cm) pole. You can align your monitors perfectly with the micro-adjustment feature.

Extend the dual articulating arms up to 18.4" (46.8 cm) to position your monitors in the ideal position. Tilt your monitors +90/-40 degrees and swivel +90/-90 degrees for ideal viewing. Rotate your displays for portrait or landscape viewing.

Neatly route your cables, keeping them organized and out of view, with the cable-management channels.

ARMDUALSS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Rotate displays to portrait orientation for web design and coding
- Position displays apart or back to back for multi-user workstations
- Ideal for health care centers, commercial and other busy environments

## Features

- **32 INCH HEAVY DUTY MONITOR STAND:** VESA 75x75/100x100mm compatible desktop multi monitor stand supports 2 large displays up to 32" (17.6lb/8kg) per screen w/horizontal articulation & height adjustment
- **WIDE RANGE OF MOTION:** Ergonomic monitor stand w/ +90/-40 tilt, +/-90 swivel, 360 rotating display, & adjustable height along 16.7" (42.4 cm) pole; Arms can rotate for back-to-back monitor setup
- **STABLE & NON-SLIP:** Aluminum free standing monitor mount w/ u-shaped base (11.8" (300mm) x 20.5" (520mm)) for max stability & flexible placement; Anti-slip rubber pads prevent scratches on desk surface
- **EASY INSTALLATION:** Dual monitor stand w/ convenient slide-and-click design makes assembling the monitor arms & VESA adapters easy, reducing the set-up time ; Align monitors w/ micro height adjustment
- **ADJUSTABLE SET UP:** Double computer monitor stand w/ cable management clips along the silver arms & center pole to organize cables for a tidy workspace & hold incl. articulation tension adjustment tool

---

### Hardware

Warranty	5 Years
Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Orientation	Horizontal
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

---

### Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Maximum Display Size	32"

Height Adjustment	Yes
Maximum Arm Extension	16.6 in [422 mm]
Display Tilt	+90 / -40
Display Swivel	+90 / - 90
Display Rotation	+180 / -180

---

#### Physical Characteristics

Color	Black & Silver
Material	Aluminum, Steel and Plastic
Product Length	33.9 in [86.0 cm]
Product Width	11.4 in [29.0 cm]
Product Height	23.2 in [59.0 cm]
Weight of Product	9.9 lb [4.5 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	12.6 in [31.9 cm]
Package Width	22.3 in [56.6 cm]
Package Height	4.3 in [10.9 cm]
Shipping (Package) Weight	11.3 lb [5.1 kg]

---

#### What's in the Box

Included in Package	2 - Swivel Arms
	1 - Pole
	1 - Base
	1 - Shoulder
	1 - Cable-Management Clip
	2 - VESA Mounts

8 - M4 x 12 mm Screws

8 - M4 x 16 mm Screws

8 - M5 x 12 mm Screws

8 - M5 x 16 mm Screws

8 - M4 x 20 mm Screws

8 - M5 x 20 mm Screws

8 - Washers

16 - Spacers

1 - 3 mm Hex Key

1 - 4 mm Hex Key

1 - 6 mm Hex Key

1 - User Manual

---

***\*Product appearance and specifications are subject to change without notice.***