

Desk Mount Monitor Arm, Up to 40-inch Screen/17.6lb (8kg), Mechanical Spring-Assisted Arm, C-Clamp/Grommet, Top-Down Installation, Toolless Adjustment

Product ID: ARMPIVOT2



This monitor desk mount creates an ergonomic workspace for productivity and supports up to a 40-inch monitor and a maximum weight of 17.6lb (8kg). The robust mechanical spring ensures long-term durability and allows for smooth arm adjustment to suit different ergonomic needs.

The uniquely design desk clamp simplifies installation by enabling users to tighten the clamp from above using a hex key or a hand drill, eliminating the need to go under the desk. In addition, the desk clamp is designed with a C-clamp and grommet mount to accommodate desks up to 2 inches (50mm) thick, providing flexibility for different desk configurations.

Mechanical spring-assisted arm enables a height adjustment range of up to 17.3in (44cm) to a maximum height of 24.4in (62cm) with effortless one-touch motion. The monitor arm can extend up to 23.3in (59.4cm) from the base of the desktop mount.

Articulating arm enables 180 pan, and the quick-release VESA plate features tool-less adjustments of +/-90 horizontal swivel, +/-90 tilt, and 360 screen rotation for portrait or landscape orientations. This flexibility enables users to customize the screen placement for maximum productivity and comfort.

Features a cable management channel along the underside of the swivel arm to keep cables out of sight. Additionally, multiple cable clips help reduce clutter and contribute to a tidy setup.

Certifications, Reports and Compatibility

Applications

Features

- **DESK MOUNT MONITOR ARM:** Single monitor mount supports up to a 40-inch display and 17.6lb (8kg); VESA plate supports 75x75/100x100mm patterns; Articulating and height adjustable steel arm; C-clamp/grommet mounting
- **EASY INSTALLATION:** Unique top-screw desk clamp for hassle-free installation without the need to go under the desk; Interchangeable C-clamp/grommet mount for desks up to 2" (5cm) thick; Includes tools for arm tension adjustment; Quick-release VESA plate
- **MECHANICAL SPRING ONE-TOUCH ADJUSTMENT:** Full-motion arm features a high-quality mechanical spring for smooth and effortless one-touch motion; Mechanical springs are more robust and resistant to wear over time compared to gas springs; Backed for 5 years
- **RANGE OF MOTION:** Toolless adjustments of +/-180 swivel, +/-90 tilt, and +/-90 screen rotation for portrait/landscape orientations; Max height 24.4" (62cm); Max arm extension 23.1" (59.4cm) from the pole; Adjustable height along the 11.1" (28.3cm) pole
- **ORGANIZED WORKSPACE:** Cable clips and a cable management channel under the arm keeps cables out of sight and help maintain a tidy setup; Keep the hex keys within arm's reach using the tool storage clip located at the back of the base

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.4 - 1.9in (1 - 5cm)

Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	17"
Maximum Display Size	40"

Fits UltraWide Displays	No
Height Adjustment	Yes
Minimum Height	7.1 in [180 mm]
Maximum Height	24.4 in [620 mm]
Minimum Arm Extension	16.5 in [419 mm]
Maximum Arm Extension	23.4 in [594 mm]
Display Tilt	+90 / - 90
Display Swivel	+90 / - 90
Swivel / Pivot	+180 / -180
Display Rotation	360
Anti-theft	No

Physical Characteristics

Color	Black
Construction Material	Steel and Plastic
Product Length	27.7 in [703 mm]
Product Width	4.5 in [115 mm]
Product Height	23.9 in [607 mm]
Weight of Product	7.9 lb [3.6 kg]

Packaging Information

Package Length	9.4 in [24.0 cm]
Package Width	17.1 in [43.5 cm]
Package Height	4.6 in [11.7 cm]
Shipping (Package) Weight	8.1 lb [3.7 kg]

What's in the Box

Included in Package	1 - Base Assembly
	1 - Spring Arm
	1 - Swivel Arm
	1 - Pole
	1 - VESA Plate
	1 - Arm Shoulder
	1 - 3mm Hex Key
	1 - 6mm Hex Key
	1 - Tool Holder
	1 - Cable Management Clip
	1 - Grommet Plate
	1 - Grommet Screw
	4 - M4x12mm Screws
	4 - M5x12mm Screws
	4 - Washers
	1 - Product Documentation

Warranty Information

Warranty	5 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***