

Single-Monitor Desk Mount - Height Adjustable - Steel

Product ID: ARMPIVOT



Save space and work in greater comfort with this monitor desk mount. The simple and stylish monitor pole lets you mount a single VESA mount monitor (75x75, 100x100) above your desk or table, and adjust the position of your display for ideal viewing.

With the computer screen mount, you can suspend your display on a support post above the desk surface and adjust your display height, position and viewing angles easily for an ergonomic work environment. The display mount gives you the added benefit of reclaiming valuable workspace on your desk. The steel single-monitor mount securely supports displays up to 34", with a maximum weight of 30.9 lb. (14 kg).

The height adjustable monitor arm features an 11.89" (302mm) tall support post, so you can adjust the height of your monitor along the pole.

Enjoy optimum viewing with easy tilt adjustment. The VESA mount can be rotated 360 degrees around the support pole to adjust your screen position. For viewing longer pages or blocks of code without scrolling, the monitor arm also supports landscape to portrait display rotation.

The display mount is made of steel for long-lasting performance.

The desk clamp monitor mount is easy to install. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk, or mount through a grommet hole. The display mount integrates a cable management hook to keep things neat.

The TAA compliant ARMPIVOT is backed by a StarTech.com 10-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount a display to a desk, table or counter to save space in commercial environments Create an ergonomic workspace in office environments Rotate your display from landscape to portrait position for web design or coding
- Create an ergonomic workspace in office environments
- Rotate your display from landscape to portrait position for web design or coding

Features

- Mount a VESA (75x75, 100x100) compatible display 12" to 34", flat screen, curved or ultrawide, with a max weight of 30.9 lb. (14 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 17.8"/45.2 cm).
- 360 rotation around the support post
- Tilts +90/-15 degrees for optimal viewing
- Adjustable monitor arm with several position/viewing angle adjustments

Hardware

Warranty	10 Years
Wallmountable	No
Articulating	No
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

Performance

Weight Capacity (Per Display)	30.9 lb [14 kg]
Maximum Display Size	34"
Fits Curved Display	Yes



Fits UltraWide Displays	Yes
Height Adjustment	Yes
Display Tilt	+90 / -15
Swivel / Pivot	360 around the support post
Display Rotation	360

Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 30.9 lb. (14 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 20" (50.8 cm).
------	---

Physical Characteristics

Color	Silver
Material	Steel and Plastic
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	4.4 lb [2.0 kg]

Packaging Information

Package Length	21.6 in [54.8 cm]
Package Width	5.7 in [14.5 cm]
Package Height	5.2 in [13.2 cm]
Shipping (Package) Weight	5.7 lb [2.6 kg]

What's in the Box

Included in Package	Support Post
	Monitor Mount
	Cable Clip



EVA Cushion

M3 (2.5mm) Allen Wrench

Large C Clamp

Small C Clamp

M6x12mm Phillips Screws

M4x15mm Phillips Screw

M5x14mm Hex Screws

Male Round Washer

Female Round Washer

Instruction Manual

Thumb Screws

Hand Screw

Pressure Plate

****Product appearance and specifications are subject to change without notice.***

