

Desk Mount Monitor Arm - VESA or Apple iMac/Thunderbolt or Ultrawide Display up to 14kg -
Articulating Height Adjustable Single Desktop Monitor Pole Mount - Clamp/Grommet

Product ID: ARMPIVOTB2



Save space with this premium desk-mount monitor arm, by suspending your display above your desk. It supports a monitor up to 30" (16:9) or up to 49" (32:9 / ultrawide), with an articulating arm that makes it easy to adjust your screen.

Use the single monitor desk mount to mount your VESA mount monitor (75x75, 100x100) up to 30" (16:9) or up to 49" (32:9 / ultrawide). You can also mount your Apple Cinema Display, 24-inch iMac or 27-inch iMac, or Thunderbolt Display that came with a removable stand or built-in VESA mount adapter. The attractive silver finish complements Apple displays, making it ideal for customer-facing workstations.

Made of aluminum, the heavy-duty monitor arm provides stable support for your display, with a weight capacity of up to 30.9 lb. (14 kg).

The arm extends 8.3" (210 mm) to allow a wide range of motion. Move the monitor arm effortlessly side to side to adjust your screen position.

With its articulating arm, the monitor mount makes it easy to find the right viewing angle. Pan a full +180/-180 degrees left or right and tilt your display +90/-15 degrees to adjust the angle up or down. For landscape or portrait viewing, rotate your display 360 degrees.

Work in comfort. This height adjustable computer monitor arm lets you raise or lower the monitor arm along the pole, with a range of up to 7.87" (200 mm).

Quick slide-and-click connections ensure easy assembly and save time when setting up multiple units. The computer screen mount gives you the option of desk-clamp or grommet-hole mounting. Hardware is included for all mounting options.

The TAA compliant ARMPIVOTB2 is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount your VESA mount display iMac, Apple Cinema and Thunderbolt Displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your display to your desk in a cubicle workstation to save space
- Create a more ergonomic workspace in the business office or home office

Features

- **HEAVY DUTY MONITOR ARM:** VESA compatible (75x75/100x100mm) desk mount monitor arm for single large 30" (16:9) or 49" (32:9) ultrawide display up to 30.9lb/14kg; Articulating & height adjustable along pole
- **APPLE DISPLAY COMPATIBILITY:** Mount also supports Apple displays such as iMac/iMac Pro/Apple Cinema/Thunderbolt Display; Aluminum construction with metallic silver finish complements your workstation
- **OPTIMAL VIEWING ANGLE:** Ergonomic monitor mount with wide range of motion including +90/-15 tilt, +/-90 swivel, 360 rotating screen (portrait/landscape), adjustable height along 6.3" pole with swiveling arm that reaches out 8.3" from base
- **EASY INSTALLATION:** Premium desktop computer monitor arm with toolless slide & click design makes assembling the monitor arm & VESA adapter easy; Pre-assembled desk clamp & pole; C-clamp/grommet
- **ORGANIZED WORKSPACE:** Desk mounted LCD/LED monitor arm with a cable management clip on the pole to organize cables & hold included articulation tension adjustment tool for a tidy setup

Hardware

Warranty	10 Years
# of Displays Supported	1
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

Performance

Weight Capacity (Per Display)	30.9 lb [14 kg]
Maximum Display Size	30" (16:9)



	49" (32:9)
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Display Rotation	360

Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 30.9 lb. (14 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 26" (66 cm).
------	---

Physical Characteristics

Product Length	12.6 in [32.0 cm]
Product Width	12.6 in [32.0 cm]
Product Height	20.5 in [52.0 cm]
Weight of Product	5.6 lb [2.5 kg]

Packaging Information

Package Length	18.3 in [46.5 cm]
Package Width	8.9 in [22.5 cm]
Package Height	5.7 in [14.5 cm]
Shipping (Package) Weight	7.2 lb [3.2 kg]

What's in the Box

Included in Package	Monitor Mount Assembly
	Swivel Arm
	Pole-and-Clamp Assembly
	Surface Protectors



Flange Mount

Torx Key

3mm Hex Key

4mm Hex Key

Access Card

Monitor Mount Screws

VESA Screws

User Manual

****Product appearance and specifications are subject to change without notice.***

