

Desk Mount Monitor Arm for Single VESA Display up to 32" or 49" Ultrawide (17.6lb/8kg) - Full Motion Articulating & Height Adjustable - C-Clamp, Grommet - Single Monitor Arm

**Product ID:** ARMPIVOTE2



This desk mount monitor arm enables you to mount and raise a monitor with a maximum screen size of 32" (16:9) or 49" (32:9) ultrawide. Its solid steel construction allows this monitor arm to support up to 17.6lb (8kg) with two mounting options (C-Clamp or Grommet mount) to securely attach your monitor to your desk.

Setup an ergonomic work environment and reclaim valuable workspace on your desk. The adjustable monitor mount lets you extend the arm a full 23.2" (590mm) from the pole. The full motion arm moves freely provides a wide range of motion across multiple axes. You can tilt the monitor +90/-85 degrees, swivel +90/-90 degrees, and even rotate 360 degrees, to find the ideal viewing angle. Switch back and forth from landscape to portrait orientation at any time. Featuring spring-assisted height adjustment, the display mount lets you raise or lower your monitor up to 13.4" (341mm) with smooth, and effortless positioning by hand. Additional adjustments with the included tools allow you to raise the monitor arm along the pole for a maximum height of 24" (610 mm) from the mounting surface.

This single desk monitor arm enables you to free up space by letting you mount your monitor to your desk, table, or countertop. In addition, it features integrated cable management channels along the arm, and cable management clips to route your cables and maintain an organized and professional look on your workstation.

With the detachable VESA plates with quick-release clips, you can mount your display to the mount with ease. Either clamp the mount to the side of a desk up to 85mm thick, table or mount it through a grommet hole on desks up to 70mm thick.

## Certifications, Reports and Compatibility

## Applications

- Mount a display to your desk, table or counter with a wide range of adjustment capability

- Grommet mount your display through a desk and position as needed
- Rotate displays to portrait orientation for web design and coding

## Features

- **DESK MOUNT MONITOR ARM:** VESA 75X75/100x100mm compatible steel monitor arm for single 17.6lb/8kg display up to 32" (16:9) or up to 49" (32:9) aspect ratio (ultrawide); Full motion articulation & height adjustable; C-Clamp / Grommet
- **FULL MOTION ARTICULATION:** The ergonomic full motion articulating arm has +90/-90 horizontal swivel, +90/-85 tilt, 360 screen rotation (portrait & landscape); Entire monitor arm can be rotated up to 360 around the pole (can be adjusted w/ incl tools)
- **ONE-TOUCH ADJUSTMENT:** Pole & arm design allows a max VESA mount height of 24" (610mm) from the desk; Gas spring assisted arm w/ height adjustable range of 13.4" (340mm) & extension up to 23.2" (590mm) from the pole; For increased comfort and productivity
- **EASY INSTALLATION:** Tighten by hand using the interchangeable desk C-clamp (0mm-85mm) or grommet mount (0mm-70mm); For desks up to 85mm thick; The monitor stand arm incl tools to adjust articulation tension; Detachable VESA plate w/ quick release clip
- **ORGANIZED WORKSPACE:** Computer monitor mount w/ cable management channels along the full motion arm to keep your cables organized; A cable clip along the pole helps you maintain a professional look with all cables hidden from sight

## Hardware

Warranty	5 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0in - 3.3in (0-85mm) Grommet Mount: Table Thickness 0in - 2.75in (0-70mm)

## Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Maximum Display Size	32" (16:9)

	49" (32:9)
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Maximum Arm Extension	23.2 in [590 mm]
Display Tilt	-85 / +90
Display Swivel	+90 / - 90
Swivel / Pivot	360 around the support pole
Display Rotation	360
Anti-theft	No

---

#### Physical Characteristics

Product Length	19.1 in [48.5 cm]
Product Width	11.4 in [29.0 cm]
Product Height	5.5 in [14.0 cm]
Weight of Product	7.4 lb [3.4 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	11.5 in [29.1 cm]
Package Width	20.3 in [51.6 cm]
Package Height	5.9 in [15.1 cm]
Shipping (Package) Weight	10.7 lb [4.9 kg]

---

#### What's in the Box

Included in Package	1 - Pole assembly
	1 - Arm assembly

- 1 - VESA mount
- 4 - M4x12mm screws
- 4 - M4x30mm screws
- 4 - Spacers
- 1 - Cable management clip
- 1 - 3mm hex key
- 1 - 4mm hex key
- 1 - 5mm hex key
- 3 - M5x6mm screws
- 1 - Cable management attachment
- 1 - Grommet plate
- 1 - Instructions manual

---

***\*Product appearance and specifications are subject to change without notice.***