

Single Desk-Mount Monitor Arm - Full Motion Articulating - Steel

Product ID: ARMPIVOTE



Add more freedom to your work day. This single desk-mount monitor arm frees up space by letting you mount your monitor above your desk or table. The full motion articulating arm makes it easy to adjust your monitor position with extension, tilt, swivel, rotation and gas-spring height adjustments.

Mounting your display on a monitor arm above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment, and reclaim valuable workspace on your desk. The single monitor mount supports 12" to 34" displays with a maximum weight capacity of 8 lb.(3.6 kg).

The adjustable monitor mount lets you extend the arm a full 22.05" (560 mm). The full motion arm moves freely provides a wide range of motion across multiple axes. You can tilt, swivel and rotate your monitor 360 degrees, to adjust your monitor for more comfortable viewing. Switch back and forth from landscape to portrait position at any time. Featuring spring-assisted height adjustment, the display mount lets you raise or lower your monitor with smooth and effortless positioning.

With its durable steel construction, the display mount securely holds your computer monitor. Setting up is easy. You can either clamp the mount to the side of your desk or table, or mount it through a grommet hole (hardware included). The integrated cable management channel keeps things neat and organized.

ARMPIVOTE is backed by a StarTech.com 2-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount a display to your desk, table or counter with a wide range of adjustment capability

- Grommet mount your display through a desk and position as needed
- Rotate displays to portrait orientation for web design and coding

Features

- Mount a VESA (75x75, 100x100) compatible display 12" to 34", flat screen, curved or ultrawide, with a max weight of 8 lb. (3.6 kg)
- Smooth one-touch height adjustment, with the gas-spring arm
- Articulating arm with wide range of motion, 360 around support pole and elbow, +/-90 degrees tilt and +/-90 degrees swivel
- Maximum arm extension of 22.05" (560 mm)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 20"/50.8 cm)

Hardware	Warranty	2 Years
	Wallmountable	No
	Articulating	Yes
	# of Displays Supported	1
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Mount Hole Size: 1.96 - 2.75 in. (50 - 70 mm)

Performance	Weight Capacity (Per Display)	8.0 lb [3.6 kg]
	Maximum Display Size	34"
	Fits Curved Display	Yes
	Fits UltraWide Displays	Yes
	Height Adjustment	Yes
	Maximum Arm Extension	22.0 in [5.6 cm]
	Display Tilt	+90 / - 90
	Display Swivel	+90 / - 90
	Swivel / Pivot	360 around the support post
	Display Rotation	360 at the elbow
		360

Special Notes / Requirements	Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 8 lb. (3.6 kg). If you choose to use an ultrawide display in portrait position, the mount
-------------------------------------	------	--

supports ultrawide displays with a max width of 20" (50.8 cm).

Physical Characteristics	Color	Black
	Material	Steel and Plastic
	Weight of Product	4.9 lb [2.2 kg]
Packaging Information	Package Length	18.8 in [4.8 cm]
	Package Width	8.4 in [2.1 cm]
	Package Height	5.2 in [1.3 cm]
	Shipping (Package) Weight	6.0 lb [2.7 kg]
What's in the Box	Included in Package	Gas Spring Arm
	Included in Package	Extension Arm
	Included in Package	Support Pole
	Included in Package	Clamp
	Included in Package	Cover and Bolt
	Included in Package	Cable Covers
	Included in Package	Spacers
	Included in Package	M4x12mm Screws
	Included in Package	M4x25mm Screws
	Included in Package	Cable Clip
	Included in Package	Plastic Gasket Cushions
	Included in Package	4mm Allen Wrench
	Included in Package	6mm Allen Wrench
	Included in Package	Instruction Manual
	Included in Package	Thumb screws
Included in Package	Cable ties	

****Product appearance and specifications are subject to change without notice.***

