

Desk Mount Monitor Arm - Heavy Duty Ergonomic VESA Monitor Arm - Single 32" (19.8lb/9kg)
Display - Full Motion, Height Adjustable, Articulating - Aluminum - C-Clamp/Grommet- Black

Product ID: ARMPIVOTHDB



Free up space while creating an ergonomic work environment. This desk-mount monitor arm makes it easy to securely mount your display above your desk or table and adjust the height with one touch. You can mount a display ranging in size from 13" to 32", and the monitor arm features an attractive black finish that complements your workspace.

This heavy-duty monitor arm saves space on your work surface by elevating your monitor above your desk or table.

The monitor-mount arm features a gas-spring cylinder that makes it easy to raise or lower your display, with up to 13.2" (335 mm) of height adjustment. Adjust the tension according to the weight of your monitor, to re-position the monitor height effortlessly.

The full-motion articulating monitor arm extends up to 23.8" (605 mm) so it's easy to find the right viewing angle. Swivel or tilt your screen +/-90 degrees for comfortable viewing or rotate it 90 degrees for landscape or portrait viewing.

The VESA monitor mount is easy to install (desk C-clamp or grommet mount) and offers built-in cable management. The detachable VESA panel makes it simple to attach or remove your monitor.

ARMPIVOTHDB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use in workstations with multiple users
- Add comfort to office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

Features

- **LARGE MONITOR MOUNT:** VESA 75x75mm/100x100mm compatible heavy-duty monitor arm for a single large 32" (16:9) or 43" (32:9/ultrawide) display up to 19.9lb/9kg; Full motion articulation & matte black finish
- **WIDE RANGE OF MOTION:** Articulating ergonomic monitor arm increases comfort & productivity w/ +/-90 tilt, +/-90 swivel, 90 rotating screen (landscape/portrait), & 360 rotating computer monitor arm
- **ONE-TOUCH ADJUSTMENT:** Max height of 19.9" from the desk, the spring-assisted LCD monitor arm offers toolless height adjustable range of 13.2" and can extend outwards up to 23.8" away from base
- **EASY INSTALLATION:** C-clamp or grommet mount by hand to a desk (10 mm to 80 mm); detachable VESA plate w/ quick release clip makes mounting displays easy; tools incl. to adjust articulation tension
- **SMALL FOOTPRINT:** Aluminum desk mount monitor arm w/ space-saving design enhances the work area & cable management channels keep cables organized & hold incl. tool for articulation tension adjustment

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.34 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

Performance

Weight Capacity (Per Display)	19.8 lb [9 kg]
-------------------------------	----------------

Minimum Display Size	13"
Maximum Display Size	32in
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Minimum Height	6.7 in [170 mm]
Maximum Height	19.9 in [505 mm]
Maximum Arm Extension	23.8 in [605 mm]
Display Tilt	+90 / - 90
Swivel / Pivot	+90 / - 90
Display Rotation	90

Physical Characteristics

Color	Black
Product Length	11.4 in [290.0 mm]
Product Width	3.9 in [10.0 cm]
Product Height	20.9 in [53.0 cm]
Weight of Product	6.2 lb [2.8 kg]

Packaging Information

Package Quantity	1
Package Length	19.2 in [48.8 cm]
Package Width	12.4 in [31.6 cm]
Package Height	4.4 in [11.2 cm]
Shipping (Package) Weight	9.2 lb [4.2 kg]

What's in the Box

Included in Package	1 - Spring Arm
---------------------	----------------

- 1 - VESA Monitor Mount
- 1 - Grommet Base Plate
- 1 - Grommet Plate
- 1 - L Bracket
- 1 - Desk Clamp
- 1 - Hex Key Holder
- 5 - Clamp Screws
- 1 - Grommet Knob
- 2 - Rubber Pads
- 1 - 4 mm Hex Key
- 1 - 5 mm Hex Key
- 1 - 6 mm Hex Key
- 4 - M4x12 mm Thumbscrews
- 4 - M5x12 mm Screws
- 4 - Washers
- 4 - Spacers
- 1 - Grommet Screw
- 1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***