

Single Monitor Stand - Adjustable - Steel - Silver

Product ID: ARMPIVSTND



This robust steel single monitor stand, with its sleek silver finish, provides secure support for your display and makes an attractive addition to your workspace. The monitor desk stand allows flexible placement of your computer screen, and is easily adjustable for ideal viewing.

The monitor mount holds your display with ease, supporting monitors from 12" to 34" up to a maximum weight capacity of 30 lb. (14kg).

For added flexibility, you can use the included hardware to mount your Apple Cinema Display, Thunderbolt Display or Apple iMac. The stand works with any Apple Cinema Display or Thunderbolt Display that came with a removable stand or built-in VESA mount adapter. It also works with the 24-inch iMac and 27-inch iMac with a removable stand, or with a built-in VESA mount adapter.

The monitor desk stand features a 15" (380 mm) tall support post, providing a wide range of height adjustment for greater comfort while you work. Adjust your display height, position and viewing angles easily to create an ergonomic work environment.

The adjustable monitor stand lets you mount a display on the desk stand, with tilt and swivel adjustments for ideal positioning. For viewing longer pages or blocks of code without scrolling, the desk monitor stand also supports landscape-to-portrait display rotation.

Made of durable steel, the single monitor mount provides easy set-up for a wide range of monitors. The integrated cable management helps to keep your cables organized and out of view.

The TAA compliant ARMPIVSTND is backed by a StarTech.com 10-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount a display on your desk, table or counter with tilt, swivel and height adjustment capabilities
- Rotate your display to portrait orientation for web design and coding

Features

- Mount a VESA (75x75, 100x100) compatible display 12" to 34", flat screen, curved or ultrawide, with a max weight of 30.9 lb. (14 kg)
- Includes hardware for mounting an iMac or Apple Cinema Display
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 25.5"/64.8 cm)
- Height adjustable monitor stand with 15" (380mm) tall support post plus position/viewing angle adjustments
- Mounting bracket pans 60 around the support post

Prominence

Warranty	10 Years
Description CDW 75 - 1st Line	StarTech.com Single Monitor Swivel Stand - For up to 34" VESA Monitors

Hardware

Wallmountable	No
Cable Management	Yes
# of Displays Supported	1
Articulating	No
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

General Specifications	ARMPIVSTND is compatible with: <ul style="list-style-type: none"> •24-inch LED Cinema Display and 27-inch LED Cinema Display •27-inch Apple Thunderbolt Display •24-inch iMac and 27-inch iMac with removable stand or built-in VESA
------------------------	---



	mount adapter
Weight Capacity (Per Display)	30.9 lb [14 kg]
Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Display Tilt	+45 / -15
Display Swivel	60
Display Rotation	360

Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 30.9 lb. (14 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 27" (68.5 cm).
------	---

Physical Characteristics

Color	Silver
Material	Steel and Aluminum
Product Length	10.2 in [26.0 cm]
Product Width	13.0 in [33.0 cm]
Product Height	4.1 in [10.5 cm]
Weight of Product	5.2 lb [2.4 kg]

Packaging Information

Package Length	21.2 in [53.8 cm]
Package Width	10.7 in [27.3 cm]
Package Height	4.6 in [11.8 cm]
Shipping (Package) Weight	7.3 lb [3.3 kg]



**What's in the
Box**

Included in Package	
	Aluminum Base
	Support Post
	Monitor Mount
	Cable Clip
	Iron Position Ring
	M5x18mm Hex Screws
	Flange
	Plastic Caps
	Torx Tool
	3mm Allen Wrench
	4mm Allen Wrench
	Access Card
	Thumb Screws
	M6x16mm Screws
	Rubber Feet
	Instruction manual

****Product appearance and specifications are subject to change without notice.***

