

Wall-Mount Monitor Arm - Full Motion - Articulating - For up to 34" (19.8lb/9kg) Displays

Product ID: ARMPIVWALL



Free up valuable desk or table space by wall-mounting your flat-panel display (TV or computer monitor). This full-motion monitor arm supports monitors and TVs up to 34" and provides effortless height and viewing angle adjustments. You can tilt, swivel, and rotate your screen, making it easy to find the perfect viewing position.

This sturdy mounting arm helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or flat-screen TV, up to 34" in size. It's ideal for many different office applications, such as healthcare or financial settings, where you may want to share your display with patients, clients, or other visitors. The wall-mountable monitor arm also works well in office settings or workspaces that back against a wall.

You can also tuck your monitor in closely to the wall, to save more space while you're not working on your computer.

The monitor arm features a gas-spring cylinder, which makes it easy to raise or lower your display. You can also adjust the tension according to the weight of your monitor, so you can re-position the monitor height at any time, with one touch. Easy one-touch height adjustment makes the monitor arm ideal for shared workspaces with multiple alternating users, such as hotel meeting rooms or office boardrooms.

The full-motion articulating arm makes it easy to find the right viewing angle. Just tilt or swivel your monitor to share your display, while collaborating with others. The articulating arm extends out to 24.4" from the wall; and it also supports a full 360-degree rotation, so it's easy to switch from landscape to portrait orientation, and back again.

The single-monitor arm makes wall-mounting your VESA compatible monitor fast and easy. It requires minimal assembly and features a built-in level, which helps you to position the arm assembly perfectly upright when mounting it to the wall. The mount also makes it easy to attach or remove your monitor with ease, and features built-in cable management to help keep your cables neat and tidy.

The ARMPIVWALL is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up desk or table space in business, commercial, industrial or office settings
- Share your monitor with clients, for easy collaboration in office settings such as healthcare, financial or real estate
- Ideal for shared workspaces with multiple users such as in hotel meeting rooms or office boardrooms
- Create space in home office settings

Features

- Wall mount a VESA (75x75, 100x100) compatible display up to 34", flat screen, curved or ultrawide, with a max weight of 19.9 lb. (9 kg)
- Tucks in closely to the wall when not in use
- Full-motion, articulating arm lets you collaborate easily, by adjusting your monitor's viewing angle to share with others
- One-touch height adjustment with gas-spring arm
- Easy monitor attachment and removal
- Simple DIY installation with built-in level

Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

General Specifications	Built-in Level: Yes
Weight Capacity (Per Display)	19.8 lb [9 kg]
Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Maximum Height	11.8 in [300 mm]
Maximum Arm Extension	24.4 in [620 mm]
Display Tilt	+90 / -65
Display Swivel	180
Display Rotation	360

Physical Characteristics

Color	Black
Product Length	24.4 in [62.0 cm]
Product Width	4.5 in [11.5 cm]
Product Height	4.3 in [10.8 cm]
Weight of Product	4.3 lb [2.0 kg]

Packaging Information

Package Quantity	1
Package Length	8.1 in [20.5 cm]
Package Width	18.7 in [47.4 cm]
Package Height	5.9 in [15.0 cm]
Shipping (Package) Weight	5.2 lb [2.4 kg]

What's in the Box

Included in Package	1 - spring arm
---------------------	----------------

- 1 - cover
- 1 - wall plate
- 1 - M5 Allen key
- 1 - M6 screw
- 2 - 6.3 x 65 mm screws
- 4 - M4x12 mm screws
- 4 - M4x25 mm screws
- 2 - anchors
- 2 - washers
- 4 - spacers
- 1 - zip tie
- 1 - instruction manual

****Product appearance and specifications are subject to change without notice.***