

Desk Mount Dual Monitor Arm with USB & Audio, Desk Clamp VESA Mount for up to 32" (17.6lb/8kg) Displays, Ergonomic Full Motion Dual Monitor Arm - Silver

Product ID: ARMSLIMDUOS



Enhance productivity and free up valuable space with the desk mount dual monitor arm. Two independent arms make it easy to adjust your dual-monitor setup.

The ARMSLIMDUOS provides easy access to two USB pass-through ports and two audio ports located at the front of the base. The ports let you plug in your microphone, headset or USB devices, without having to reach for your computer.

The desk-mount monitor arms offer a full range of motion on several axes, letting you tilt, pan and rotate your monitors to adjust your viewing angle. The dual-arm monitor mount holds two 15" to 32" monitors and each arm supports up to 8.0 kg (17.6 lb.) of weight.

With its durable aluminum construction and stylish silver finish, the ARMSLIMDUOS securely holds two monitors using a standard VESA 75x75 and 100x100 mount.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ARMSLIMDUOS is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Spread displays apart or position them back-to-back for multi-user workstations
- Mount dual displays to the side of your desk or table, with a wide range of adjustment capability
- Ideal for busy work environments such as health care centers, financial and commercial environments
- Rotate displays to portrait orientation for web design and coding

Features

- **32 INCH LARGE MONITOR SUPPORT:** VESA 75x75/100x100mm compatible full motion multi monitor mount supports 2 displays up to 32" (17.6lb/8kg) per arm; 2 USB 2.0 passthrough ports, 2x 3.5mm audio/mic jacks
- **EASY INSTALLATION:** This silver monitor mount has a detachable VESA plate w/ quick release clip that makes mounting displays easy & tools incl. for arm balance & tightening c-clamp to desk (up to 60mm)
- **CONVENIENT CONNECTIVITY:** This desktop monitor mount arm incl. 2 USB-A 2.0 (480Mbps) & 2 3.5mm ports that extend your PC/laptop/computer/dock ports for connecting devices & built-in cable management
- **TILT SWIVEL ROTATING:** Desk mount dual monitor arm increases ergonomic comfort & productivity w/ -90/+85 tilt, +/-90 swivel & articulating arms support 360 degree screen rotation (landscape/portrait)
- **ONE-TOUCH ADJUSTMENT:** Max height of 17.7" from the desk, the spring-assisted monitor arm offers toolless adjustable height range of 13.9" and can extend outwards up to 17.7" away from base

Hardware

Warranty	2 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Max Table Thickness 3.35 in. (85 mm)

Performance

Weight Capacity (Per	17.6 lb [8 kg]
----------------------	----------------

Display)	
Minimum Display Size	15"
Maximum Display Size	32"
Height Adjustment	Yes
Maximum Arm Extension	0.0 in [0 mm]
Maximum Arm Span	0.0 in [0 mm]
Display Tilt	-90 / +85
Display Swivel	+180 / -180
Swivel / Pivot	+/- 170 at the base +/- 180 at the shoulder +/- 90 at the elbow
Display Rotation	360

Physical Characteristics

Color	Silver
Material	Aluminum
Product Length	29.1 in [74 cm]
Product Width	7.5 in [19 cm]
Product Height	5.1 in [13 cm]
Weight of Product	13.7 lb [6.2 kg]

Packaging Information

Package Quantity	1
Package Length	9.8 in [24.8 cm]
Package Width	31.9 in [81.1 cm]
Package Height	5.7 in [14.6 cm]
Shipping (Package) Weight	17.0 lb [7.7 kg]

What's in the Box

Included in Package	1 - Mounting Arm
	1 - Desk Clamps (Upper Bracket)
	1 - desk clamps (lower bracket)
	1 - VESA Monitor Mounts
	8 - M4x12 mm screws
	8 - M4x30 mm screws
	8 - Plastic Spacers
	1 - M4 Hex Key
	1 - M5 Hex Key
	8 - M6x12mm screws
	4 - M8x12 mm screws
	2 - rubber pads
	1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***