

Sit Stand Desk Converter with Keyboard Tray - Large 35" x 21" Surface - Height Adjustable
Ergonomic Desktop/Tabletop Standing Workstation - Holds 2 Monitors - Pre-Assembled

Product ID: ARMSTSLG



This sit-stand desk converter, featuring a large work surface, lets you change your working position with ease, to enhance your comfort and productivity.

With a simple squeeze of a paddle, you can easily switch your position to sitting or standing, to keep a balanced level of movement. The workstation features a pneumatic spring arm that provides effortless movement - you simply raise or lower the platform with one squeeze of the lever. You can adjust the standing desk to match your exact height requirements, with a height adjustment range of 15.7" (399 mm).

Create an ergonomic work space at a fraction of the cost of a standing desk. Simply place the sit-stand desk converter on your existing work surface (minimum 26" depth), to enjoy the benefits of a height-adjustable standing desk.

With a large 35" (wide) work surface, the sit-stand workstation gives you plenty of setup options, supporting two monitors (up to 24" each), or one monitor (up to 30"), with a generous weight capacity of 12.7 kg (28.1 lb.).

You can also use the grommet hole and provided hardware to mount a monitor arm to the workstation. It supports many StarTech.com monitor arms including ARMDUAL, ARMPIVOT and ARMSLIM.

The ARMSTSLG is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a sit-stand workstation with versatile applications in office settings, cubicle environments, corporate business and institutions, or the home office
- Provides a cost-effective solution for enhancing ergonomics by utilizing existing desks and work surfaces
- Mount a monitor arm to the workstation, using the grommet hole and provided hardware

Features

- **SIT STAND DESK CONVERTER:** Equipped w/ a lever-controlled pneumatic spring and smooth adjustable height that can be locked at any position between 6.3" and 22" (160mm & 560mm) from the desk's surface
- **NO ASSEMBLY:** Convert desktop/tabletop into a sit-stand workstation w/large 35.4"x20.9" surface that has space for two 24" monitors on standard stands; Requires 35.4"x26" surface, holds 28lb (12.7kg)
- **STURDY KEYBOARD TRAY:** The surface area of 26.8" x 10.4" and weight capacity of 5lb, can fit a full size keyboard and mouse; w/ the included tools it can be adjusted to the user's ideal position
- **GROMMET MONITOR MOUNTING:** Ergonomic stand up desk converter w/incl grommet mounting hardware is compatible w/monitor arms like ARMDUAL/ARMPIVOT/ARMSLIM to support multiple displays (28lb total weight)
- **CABLE MANAGEMENT:** Standing desk converter w/ multiple integrated cable management loops to ensure cables are organized; Grommet hole cap with an entry point incl. for additional cable management

Hardware

Warranty	2 Years
Cable Management	Yes
Mounting Options	Grommet Hole Mount

Performance

General Specifications	Height Adjustment Range of Sit-Stand Workstation: 15.7 in [399 mm]
Weight Capacity of Work Surface	28.0 lb [12.7 kg]
Weight Capacity of Keyboard Tray	5.1 lb [2.3 kg]
Height Adjustment	Yes
Maximum Height	22.0 in [560 mm]

Special Notes / Requirements

Note	The keyboard tray (26.8" x 10.4") has a weight capacity of 5 lb.
------	--

(2.3 kg).

Physical Characteristics

Color	Black
Keyboard Tray Width	26.8 in [680 mm]
Keyboard Tray Depth	10.4 in [265 mm]
Product Length	26.2 in [66.6 cm]
Product Width	35.4 in [90.0 cm]
Product Height	6.3 in [16.0 cm]
Weight of Product	39.8 lb [18.1 kg]

Packaging Information

Package Quantity	1
Package Length	3.4 ft [1.0 m]
Package Width	31.7 in [80.6 cm]
Package Height	8.6 in [21.8 cm]
Shipping (Package) Weight	48.5 lb [22.0 kg]

What's in the Box

Included in Package	1 - sit-stand workstation
	1 - small hex key
	1 - large hex key
	1 - clamp plate
	1 - M10 x 50 mm bolt
	1 - / - 16 x 50 mm bolt
	1 - instruction manual

****Product appearance and specifications are subject to change without notice.***