

Wall-Mount Monitor Arm - 10.2" (26 cm) Swivel Arm - Premium

Product ID: ARMWALLDS2



Free up space with this wall-mount monitor arm and enjoy optimum viewing with the swiveling extension arm. The premium design ensures smooth, effortless motion and makes it easy to re-position your display, to work in comfort or collaborate with others. The attractive silver finish complements your decor. The wall-mount system is ideal for business, healthcare, financial or other settings, where you may want to share your screen, or for customer-facing interactive displays.

The wall-mount monitor arm extends 10.2" (26 cm), making it easy to change your screen position. Move the swivel wall-mount freely, to the left or right. You can also adjust the swivel tension.

The robust aluminum design provides a stable wall-mount for your computer monitor or flat-screen TV up to 34". It's ideal for touch-screen stability. The universal display wall mount supports VESA mount monitors (75x75, 100x100) up to 30.9lb. (14 kg) in weight.

Share your screen with ease. The display wall mount offers a full +180-degree/-180-degree pan, to move your screen left or right. It tilts freely +90/-15-degrees, to adjust the angle up or down. Rotate your screen for landscape or portrait viewing.

Push the swivel arm back to the wall, so your monitor sits just 5" (129 mm) from the wall when not in use.

The quick slide-and-click connections make the monitor wall mount easy to assemble and saves time when setting up multiple units.

The TAA compliant ARMWALLDS2 is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up space in business, commercial, industrial or office settings
- Share your screen with clients or visitors in office settings such as healthcare or financial
- Works well in non-desk environments as well as public places

Features

- Wall mount a VESA (75x75, 100x100) compatible display up to 34", flat screen, curved or ultrawide, with a max weight of 30.9 lb. (14 kg)
- Swivel arm extends 10.2" (26 cm) and features two swivel points for flexible viewing
- Easy tool-less assembly with quick slide-and-click connections
- Adjust your viewing angle with +180/-180 pan, +90/-15tilt, and rotation
- Robust and stable aluminum design

Hardware	Warranty	10 Years
	Cable Management	Yes
	Articulating	No
	# of Displays Supported	1
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
Performance	Weight Capacity (Per Display)	30.9 lb [14 kg]
	Minimum Display Size	13"
	Maximum Display Size	34"
	Fits Curved Display	Yes
	Fits UltraWide Displays	Yes
	Height Adjustment	No
	Maximum Arm Extension	10.2 in [2.6 cm]
	Display Tilt	+90 / -15
	Display Swivel	+180 / -180
	Swivel / Pivot	+180/-180 at the wall
	Display Rotation	360 at the elbow
		360
Physical Characteristics	Color	Silver
	Material	Aluminum

Product Length	15.6 in [4.0 cm]
Product Width	9.4 in [2.4 cm]
Product Height	4.5 in [1.2 cm]
Weight of Product	5.4 lb [2.5 kg]

Packaging Information	Package Length	13.4 in [3.4 cm]
	Package Width	7.4 in [1.9 cm]
	Package Height	3.9 in [100.000 mm]
	Shipping (Package) Weight	7.5 lb [3.4 kg]

What's in the Box	Included in Package	Wall Mount
	Included in Package	Swivel Arm
	Included in Package	Monitor Mount
	Included in Package	M3 Hex Key
	Included in Package	Thumb Screws
	Included in Package	User Manual
	Included in Package	Wall Plugs
	Included in Package	Mounting Screws

****Product appearance and specifications are subject to change without notice.***

