

2U Rack Blank Panel for 19in Server Racks and Cabinets

Produkt ID: BLANKB2



The BLANKB2 2U Rack Blank Panel for 19in Server Racks and Cabinets is designed to EIA RS-310-C specifications and fits all 19" standard server racks and cabinets.

Ideal for improving airflow within the rack by covering the unused spaces, the filler panel/blank panel is constructed of cold-rolled steel and features a black powder coated finish that matches most industry standard black server cabinets and racks.

Certifikat, rapporter och kompatibilitet

Användning

- Assist with directing air flow
- Filling in the spaces when no other rack mounted equipment is needed

Funktioner

- Powder black coloring to match most rack and cabinets
- SPCC Cold Rolled Steel, 1.2mm thick

Hårdvara

Garantipolicy

Lifetime

Ramtyp	Stål
U-höjd	2U
Industristandarder	EIA RS310-C

Utseende

Färg	Svart
Produktlängd	0.0 in [0.0 mm]
Produktbredd	0.0 in [0.0 mm]
Produkthöjd	0.0 in [0.0 mm]
Produktvikt	16.9 oz [479.9 g]

Förpackning

Package Length	19.4 in [49.4 cm]
Package Width	4.0 in [10.1 cm]
Package Height	0.8 in [21.0 mm]
Fraktvikt (förpackning)	19.2 oz [545.0 g]

Vad det är i lådan

Ingår i paketet	2 U Blanking Plate
	Package of M6 Screws and Cage nuts (4 sets)

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

