

2U Rack Blank Panel for 19in Server Racks and Cabinets

Product ID: BLANKB2



The BLANKB2 2U Rack Blank Panel for 19in Server Racks and Cabinets is designed to EIA RS-310-C specifications and fits all 19" standard server racks and cabinets.

Ideal for improving airflow within the rack by covering the unused spaces, the filler panel/blank panel is constructed of cold-rolled steel and features a black powder coated finish that matches most industry standard black server cabinets and racks.

Certifications, Reports and Compatibility

Applications

- Assist with directing air flow
- Filling in the spaces when no other rack mounted equipment is needed

Features

- Powder black coloring to match most rack and cabinets
- SPCC Cold Rolled Steel, 1.2mm thick

Hardware

Warranty	Lifetime
Frame Type	Steel

U Height	2U
Industry Standards	EIA RS310-C

Physical Characteristics

Color	Black
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	16.9 oz [479.9 g]

Packaging Information

Package Length	19.4 in [49.4 cm]
Package Width	4.0 in [10.1 cm]
Package Height	0.8 in [21.0 mm]
Shipping (Package) Weight	19.2 oz [545.0 g]

What's in the Box

Included in Package	2 U Blanking Plate
	Package of M6 Screws and Cage nuts (4 sets)

****Product appearance and specifications are subject to change without notice.***

