

## Sit-Stand Desk Converter with Monitor Arm - 35" Wide Work Surface - For up to 30" Monitor

**Product ID:** BNDSTSLGPVT



The sit-stand desk converter with pole-style monitor arm enhances your productivity and comfort. This ergonomic desk solution includes two products: the spacious sit-stand workstation (ARMSTSLG) and the single monitor mount (ARMPIVOT), supporting a monitor up to 30". The monitor mount provides extended height adjustment along the pole, and tilts for optimum viewing.

With one touch, switch your position from sitting to standing or vice versa, to keep a balanced level of movement throughout the day. The height-adjustable standing desk workstation features a pneumatic spring that makes it easy to raise or lower your work surface up to 15.7" (400 mm), to suit your height requirements (instead of selecting from pre-determined heights). You can also adjust the tension, to make height adjustments even easier.

The included monitor mount features a support post that's 11.89" (302 mm) tall, for a much greater height-adjustment range than a typical monitor stand can provide. Adjust your viewing angle with +90/-15 tilt. The monitor mount also supports landscape-to-portrait display rotation.

Simply place the sit-stand desk converter on your existing desk (minimum 26" depth). Then, attach the monitor mount using the grommet hole and included grommet-mount hardware.

The BNDSTSLGPVT is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Create a single monitor sit-stand workstation for business, corporate, institutional, or home office use
- Install ergonomic desk solutions while saving cost by utilizing existing desks and work spaces

## Features

- Place the sit-stand workstation on your existing desk to create an ergonomic stand-up desk, with spacious 35" (0.9 m) wide work surface
- Lever-controlled pneumatic spring for easy height adjustment (max height adjustment range: 15.7")
- Single monitor mount supports one monitor up to 30"
- Arm offers wide range of height adjustment along the pole, up to 11.89 in. (302mm)
- Monitor arm provides +90/-15 tilt, and 360 rotation around the support post
- Minimum footprint: 660 mm (26") D x 889 mm (35") W
- Sit-stand workstation features high-quality construction, engineered with steel and MDF wood base, tray and work surface
- Straight up and down movement, provides a stable workstation with no fear of tipping

---

### Hardware

Warranty	2 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Grommet Hole Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

---

### Performance

General Specifications	Height Adjustment Range of Sit-Stand Workstation: 15.7 in [399 mm]
	Height Adjustment Range of Monitor Arm: up to 11.89 in/302mm
	Weight Capacity of Work Surface: 28.1 lb [12.7 kg]
	Weight Capacity of Work Surface with Single Monitor Arm: 23.7 lb [10.7 kg]
Weight Capacity (Per Display)	24.3 lb [11 kg]
Weight Capacity of	5.1 lb [2.3 kg]



Keyboard Tray	
Maximum Display Size	30in
Height Adjustment	Yes
Display Tilt	+90 / -15
Swivel / Pivot	360 around the support post
Display Rotation	360

---

**Physical Characteristics**

Color	Black
Material	Steel, MDF Wood and Plastic
Keyboard Tray Width	26.8 in [68 cm]
Keyboard Tray Depth	10.4 in [26.5 cm]
Product Length	26.4 in [67 cm]
Product Width	35.0 in [88.9 cm]
Product Height	6.3 in [16 cm]
Weight of Product	44.3 lb [20.1 kg]

---

**Packaging Information**

Shipping (Package) Weight	54.5 lb [24.7 kg]
---------------------------	-------------------

---

***\*Product appearance and specifications are subject to change without notice.***

