

Sit-Stand Desk Converter with Monitor Arm - 35" Wide Work Surface - For up to 26" Monitor

**Product ID:** BNDSTSLGSLIM



The sit-stand desk converter with single monitor arm helps enhance your productivity and comfort. This ergonomic desk solution includes two products: the spacious sit-stand workstation (ARMSTSLG) and the articulating monitor mount (ARMSLIM), supporting a display up to 26". The slim and stylish monitor arm frees up desk space and offers a full range of motion, adjusting easily for ideal viewing.

With one touch, switch your position from sitting to standing, to keep a balanced level of movement throughout the day. The height-adjustable standing desk workstation features a pneumatic spring that makes it easy to raise or lower your work surface up to 15.7" (400 mm), to suit your height requirements. You can also adjust the tension, to make height adjustments even easier.

The articulating monitor arm makes it easy to adjust your display for perfect viewing. You can extend the arm up to 23.46" (596 mm) and tilt, pan, and swivel your display with a full range of motion. The arm's spring-assisted height adjustment allows easy positioning, with a maximum range of up to up to 14.17" (360 mm). The arm also rotates for landscape or portrait viewing.

Simply place the sit-stand desk converter on your existing desk (minimum 26" depth). Then, attach the monitor mount using the grommet hole and included grommet-mount hardware.

The BNDSTSLGSLIM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Create a single monitor sit-stand workstation for business, corporate, institutional, or home office use
- Install ergonomic desk solutions while saving cost by utilizing existing desks and work spaces

## Features

- Place the sit-stand workstation on your existing desk to create an ergonomic stand-up desk, with spacious 35" (0.9 m) wide work surface
- Lever-controlled pneumatic spring for easy height adjustment (max height adjustment range: 15.7")
- Single monitor mount supports one monitor up to 26", and offers wide range of height adjustment, up to 14.17" (360 mm)
- Articulating arm with wide range of motion (+90/-65 tilt, 360 swivel at the elbow, and +/- 90 display rotation)
- Maximum arm extension of 23.46" (596 mm)
- Minimum footprint: 660 mm (26") D x 889 mm (35") W
- Sit-stand workstation features high-quality construction, engineered with steel and MDF wood base, tray and work surface
- Straight up and down movement, provides a stable workstation with no fear of tipping

---

### Hardware

Warranty	2 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Grommet Hole Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

---

### Performance

General Specifications	Height Adjustment Range of Sit-Stand Workstation: 15.7 in [399 mm]
	Height Adjustment Range of Monitor Arm: up to 14.17 in [360 mm]
	Weight Capacity of Work Surface: 28.1 lb [12.7 kg]
	Weight Capacity of Work Surface with Single Monitor Arm: 23.7 lb [10.7 kg]
Weight Capacity of Keyboard Tray	5.1 lb [2.3 kg]



Maximum Display Size	26in
Height Adjustment	Yes
Minimum Height	6.3 in [16 cm]
Maximum Height	22.0 in [56 cm]
Maximum Arm Extension	23.5 in [59.6 cm]
Display Tilt	+90 / -65
Display Swivel	360
Swivel / Pivot	180 around the support post 360 at the elbow
Display Rotation	+90 / - 90

---

**Physical Characteristics**

Color	Black
Material	Steel, MDF Wood and Plastic
Keyboard Tray Width	26.8 in [68 cm]
Keyboard Tray Depth	10.4 in [26.5 cm]
Product Length	26.4 in [67 cm]
Product Width	35.0 in [88.9 cm]
Product Height	6.3 in [16 cm]
Weight of Product	44.3 lb [20.1 kg]

---

**Packaging Information**

Shipping (Package) Weight	58.2 lb [26.3 kg]
---------------------------	-------------------

---

***\*Product appearance and specifications are subject to change without notice.***

