

10ft (3m) Heavy Duty Power Extension Cord, Locking C14 to Locking C13, PDU Power Cord, 15A 250V, 14AWG, AC Power Cable Extension, TAA Compliant, UL Listed

Product ID: C14LC13L14G15ABK10FT



The IT Pro's Choice

StarTech's power cables are designed by and for IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using ETL listed components
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions
- Backed for life with free lifetime 24/5 multi-lingual technical assistance

StarTech is trusted throughout the IT ecosystem and used by over 90% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

Features

- **Deliver Reliable Power**: Connect servers, network equipment, and rack-mounted hardware to a PDU using this 10ft (3m) Locking C14 to Locking C13 power extension cord; Built with 14AWG 100% copper wire and rated for up to 250V at 15A
- **Minimize Power Interruptions**: Maintain uptime for mission-critical equipment with locking C13 and C14 connectors that resist vibration, tension, and accidental unplugging; Reduces power loss risk when extending PDU connections
- **Ensure Certified Electrical Safety**: Support professional deployments with a UL Listed power cord featuring a VW-1 flame-rated jacket; Flexible SJTW jacket enables clean and safe routing through dense racks and cable trays
- **Replace Aging Power Cables**: Eliminate unreliable power cords with a locking cable that stays securely connected; IEC 60320 C14 connects to rackmount PDUs and C13 supports servers, switches, and workstations; TAA Compliant
- **The IT Pro's Choice**: Our power cords are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and compatibility across a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

Power

Input Voltage	250V AC
---------------	---------

Input Current	15A
---------------	-----

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.4 in [10.0 mm]
Product Length	10.0 ft [3.0 m]
Product Width	2.1 in [5.3 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	1.1 lb [0.5 kg]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	10.8 in [27.4 cm]
Package Height	2.0 in [5.0 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 10ft Locking C14 to Locking C13 Power Cord
---------------------	--

**Product appearance and specifications are subject to change without notice.*