
Shielded Cat6a Keystone Jack, 10-Pack RJ45 Ethernet Keystone Jacks, STP Cat6a Wall Jack, 180-Degree Toolless

Product ID: C6AKEYTLSTP18010PK



Use this 10-pack of Shielded Toolless RJ45 Keystone Jacks to terminate network drops quickly and cleanly without punch down tools. Ideal for structured cabling installations requiring EMI protection, this Cat6a keystone jack multipack provides a reliable solution for terminating shielded cable runs to patch panels and wall plates.

The Toolless Cat6a Keystone Jack features a 180-degree layout that supports straight cable entry from the rear, suitable for keystone patch panels and wall plates with open clearance. This layout enables clean, straight-through terminations without re-positioning the cable.

Maintain signal integrity in high-density installations with a zinc alloy housing and nickel-plated shielding designed to minimize EMI. Gold-plated phosphor bronze RJ45 contacts ensure stable connectivity, for long-term reliability in high-uptime networks and demanding environments.

Plan and execute multi-room cabling projects with consistent hardware at every drop point. The 10-pack format enables standardized terminations across floors, rooms, and offices, eliminating variability from mixed stock and ensuring consistency across larger LAN deployments.

Certifications, Reports and Compatibility

Applications

Features

• Terminate STP Cable Runs: Use this 10-pack of Shielded Toolless Cat6a RJ45 STP keystone jacks to quickly terminate shielded network cable drops; This multipack is ideal for secure terminations to patch panels and wall plates across critical LAN infrastructure

• Fit Rackmount Panel Layouts: Toolless Cat6a keystone jack has a 180-degree orientation to support straight rear cable terminations; Ideal for patch panels and wall plates where in-line orientation is preferred and rear clearance is not a constraint

• Simplify Wiring Connections: Terminate RJ45 wiring in T568A or T568B configurations without punch down tools; Wiring schemes are printed on the jack for quick reference; Toolless design enables quick installation and reconfiguration when needed

• Standardize Network Compatibility: Enable 10Gbps Ethernet and up to 100W PoE (IEEE 802.3bt Type 4) over Cat6a STP; Gold-plated contacts enhance conductivity and meets ANSI/TIA-568-C.2 standards; Backward compatible with Cat5e in mixed-cable environments

• The IT Pro's Choice: Our network jacks, connectors, and couplers are tested for peak performance in structured cabling environments; Designed for reliability with consistent fit and finish; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030918015
	Package Quantity	10
	Warranty	3 Years
Power		
	Power Delivery	100W
Physical & Environmental		
	Color	Silver
	Material	Polycarbonate
		Nickel-plated Zinc
	Product Length	1.5 in [37.6 mm]
	Product Width	0.6 in [16.5 mm]
	Product Height	0.9 in [21.6 mm]
	Weight of Product	0.8 oz [24 g]
	Operating Temperature	-10&degC to 60&degC (14&degF to 140&degF)

	Storage Temperature	-40&degC to 70&degC (-40&degF to 158&degF)
	Humidity	85%
Hardware		
	Connector Plating	Gold
	Wiring Standard	TIA/EIA-T568A
		TIA/EIA-T568B
	Industry Standards	IEEE 802.3 10/100/1000BASE-T
		IEEE 802.3bz 2.5GBASE-T
		IEEE 802.3bz 5GBASE-T
		IEEE 802.3ae 10GBASE-T
		IEEE 802.3bt Type 4 (4PPoE)
Packaging & In-the-Box		
	Included in Package	10 - Cat 6a Keystone Jack
		10 - Wire Cap
		10 - Dust Cover
		1 - Quick-Start Guide
	Package Width	3.3 in [85 mm]
	Package Depth	7.0 in [17.8 cm]
	Package Height	1.7 in [43 mm]
	Shipping (Package) Weight	10.9 oz [308 g]

Product appearance and specifications are subject to change without notice.