

10 ft Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch Cable

Product ID: C6CROSS10YL



StarTech.com's Cat 6 UTP Crossover Patch Cables offer reliable Ethernet connections. This 10ft cable is ETL verified to meet or exceed all Category 6 performance standards, and features a durable yellow jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

Featuring top quality construction (100% copper conductors, 23 Gauge Wire and 50 Micron gold connectors), our Cat6 Crossover cables are built to last and backed by lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Use crossover cable to directly connect two computers without the need for a hub
- Connect two Ethernet hubs/switches together with crossover cable
- Category 6 cables support gigabit networks

Features

- StarTech.com Category 6 crossover cables are manufactured to meet or exceed CAT6 specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification
- Molded ends with top-quality connectors

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Crossover Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Yellow
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]

Packaging Information

Package Length	7.9 in [20 cm]
Package Width	8.5 in [21.6 cm]
Package Height	1.0 in [25 mm]
Shipping (Package) Weight	4.6 oz [130 g]

What's in the Box

Included in Package	10 ft. Yellow Category 6 Crossover Cable
---------------------	--



**Product appearance and specifications are subject to change without notice.*

