

## 1m Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch Cable

**Product ID:** C6CROSS1MYL



The C6CROSS1MYL Cat6 Crossover Cable (1m) meets or exceeds all Category 6 cable specifications, to ensure reliable Gigabit network connections and features a durable yellow PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 crossover cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Crossover Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat 6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Ethernet crossover cable is constructed with 24 gauge copper wire, to support a broad range of network applications, such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat6 cable offers high quality connectors, comprised of 50-micron gold to deliver optimum conductivity while eliminating signal loss that results from oxidation or corrosion.

## Certifications, Reports and Compatibility

## Applications

- Designed for use with Gigabit networks
- Directly connecting two computers together without the need for a hub
- Connecting two Ethernet hubs/switches

## Features

- Molded RJ45 connectors
- Carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire
- ETL Verified

---

### Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Crossover Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

---

### Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

---

### Connector(s)

Connector A	RJ-45
Connector B	RJ-45

---

### Physical Characteristics

Color	Yellow
Wire Gauge	24 AWG



Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100 cm]
Weight of Product	1.6 oz [45 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	2.0 oz [56 g]

---

**What's in the Box**

Included in Package	1 m Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

